

Extreme Solarization-Resistant Reflection/Backscatter Probe

See More by [Ocean Optics](#)



Stock #90-566 **NEW** 1 In Stock

⊖ 1 ⊕ **\$3,232⁰⁰**

ADD TO CART

Volume Pricing

Qty 1+	\$3,232.60 each
Need More?	Request Quote

Product Downloads

General

QR450-7-XSR **Model Number:**

Extreme Solarization-Resistant
Reflection/Backscatter Probe **Title:**

Optical Properties

180 - 1100 **Wavelength Range (nm):**

Regulatory Compliance

[Compliant](#) **RoHS 2015:**

[View](#) **Certificate of Conformance:**

[Compliant](#) **Reach 250:**

Product Details

- Versatile Sampling for Diffuse/Specular Reflectance, Backscatter & Fluorescence
- VIS-NIR (400–2100nm) and UV-VIS (180–1100nm) Solarization-Resistant Models
- Extreme Solarization-Resistant (XSR) Probe Features Ultra-Low Loss Fiber for Harsh UV Exposure
- Connects Directly with Ocean Optics Spectrometers & Accessories

Ocean Optics Reflection/Backscatter Probes are compact, fiber-coupled sampling tools for measuring diffuse and specular reflectance, backscatter, or fluorescence in solids, solutions, or powders, and connect directly with [Ocean Optics Spectrometers and Accessories](#). They provide quantitative insights into a sample's color, appearance, and chemical composition. Choose from Visible-NIR, Solarization-Resistant, or XSR models for applications ranging from routine reflectance to demanding UV measurements. With durable jacketing, precision ferrules, and solarization-resistant fiber, the rugged design ensures reliable performance even in harsh conditions. Ocean Optics Reflection/Backscatter Probes can be optimized for UV applications, with the XSR probe featuring ultra-low loss fiber designed to withstand harsh UV exposure.