

IDS GV-50C0SE-M-GL, GigE, 1/2.3" Monochrome Camera

See More by [IDS Imaging Development Systems](#)



IDS Imaging uEye+ GigE Cameras



Stock **#26-256** 1 In Stock

-

1

+

S\$1,001⁰⁰

ADD TO CART

Volume Pricing	
Qty 1+	S\$1,001.00 each
Need More?	Request Quote

Product Downloads

SPECIFICATIONS

General

Type:

Monochrome Camera

Model Number:

GV-50C0SE-M-GL	
IDS Imaging Development Systems	Manufacturer:
uEye+ SE	Camera Series:
Monochrome	Spectrum:
Physical & Mechanical Properties	
34 x 44 x 47 (excludes connectors and lens mount)	Dimensions (mm):
105	Weight (g):
Full	Housing:
Sensor	
128MB	Image Buffer:
1/2.3"	Sensor Format:
2.35	Resolution (Megapixels):
52.00	Frame Rate (fps):
1,936 x 1,216	Pixels (H x V):
3.45 x 3.45	Pixel Size, H x V (µm):
6.679 x 4.195	Sensing Area, H x V (mm):
Sony IMX392	Imaging Sensor:
Progressive Scan CMOS	Type of Sensor:
Global	Shutter Type:
12 bit	Pixel Depth:
0.025ms - 2000ms	Exposure Time:
71.00	Dynamic Range (dB):
GigE Vision	Machine Vision Standard:
Electrical	
1.5 - 3.7	Power Consumption (W):
Hardware & Interface Connectivity	
GigE (PoE)	Interface:
GigE RJ45, screwable	Connector:
Power over Ethernet (PoE) or 12 - 24VDC via GPIO with #16-016	Power Supply:
2 Flash Output, 2 Trigger Input, 2 GPIO, 1 Voltage Output, 1 Ground	GPIOs:
Hardware Trigger (GPIO); Software Trigger	Synchronization:
Back Panel	Interface Port Orientation:
8-pin Hirose connector (HR25-7TR-8PA(73))	GPIO Connector Type:
Threading & Mounting	
C-Mount	Mount:
1/4-20 with Tripod Mount Adapter #16-017	Mounting Threads:
Environmental & Durability Factors	

0 to +55	Operating Temperature (°C):
-20 to +60	Storage Temperature (°C):
Regulatory Compliance	
Exempt	RoHS 2015:
View	Certificate of Conformance:
Contains SVHC(s)	REACH 241:

PRODUCT DETAILS

- Standard (SE) and Compact (CP) Housing Options Available
- C-Mount with Large Format CMOS Sensors up to 1.1"
- GenICam GigE Vision Compliant
- [IDS Imaging uEye CP/XCP/SE USB3 Cameras](#) Available

IDS Imaging uEye CP/SE GigE Cameras utilize IDS Imaging's [peak SDK platform](#) that supports GeniCam and GigE Vision standards for ease of software development and integration. The CP cameras are the industry standard size of 29 x 29 x 29mm and work for almost any application. The SE cameras have a larger housing size of 34 x 44 x 47mm to allow for exceptional heat management and are ideal for noise and heat sensitive applications. IDS Imaging uEye CP/SE GigE Cameras feature a screwable 8-pin Hirose connector for trigger and flash as well as two GPIOs. These cameras are ideal for a variety of applications such as automation, automotive, medical technology, and logistics.