


## Hydrogen Cyanide Fiber-Coupled Gas Cell, 16.5 cm Path Length, SC/PC



Stock #72-203 **1 In Stock**

⊖ 1 ⊕ **S\$1,435<sup>00</sup>**

**ADD TO CART**

### Volume Pricing

Qty 1-4	<b>S\$1,435.00</b> each
Qty 5-9	<b>S\$1,291.50</b> each
Need More?	<a href="#">Request Quote</a>

### Product Downloads

16.5 Path Length (cm):

SC/PC Fiber Connector Type:

### General

Hydrogen Cyanide (H<sup>13</sup>C<sup>14</sup>N) Type:

HCN-13-H(16.5)-25-SCPC Model Number:

### Optical Properties

---

1525 - 1565 **Wavelength Range (nm):**

>50 **Transmission (%):**

## Environmental & Durability Factors

0 to +70 **Operating Temperature (°C):**

## Regulatory Compliance

[View](#) **Certificate of Conformance:**

---

## Product Details

- Hydrogen Cyanide and Acetylene Gasses Available for Wavelength Coverage of 1510 to 1565nm
- FC and SC Fiber Connection Options with a Variety of Path Lengths Available
- NIST Traceable Reference Cells

Wavelength References Fiber-Coupled Gas Cells are FC/APC, SC/APC, FC/PC, or SC/PC connected fiber coupled, gas filled precision filters whose absorption wavelengths depend on specific molecular energy level transitions that may be used as wavelength standards. Hermetically sealed to maintain >10 year lifetime, these gas cells feature metal housings, wedged windows, and coated optics for minimum interference artifacts and can be easily integrated into existing benchtop systems. Wavelength References Fiber-Coupled Reference Cells are available with a variety of path lengths and pressures which meet the requirements of NIST Standard Reference Material® (SRMs) 2517a, 2519, or 2519a. Short path lengths are recommended for measuring gasses at high concentration while longer path lengths enable more sensitive measurements. These reference cells are ideal for spectroscopy, wavelength/frequency locking, laser calibration, and optical gas sensing systems. Hydrogen Cyanide ( $H^{13}C^{14}N$ ) has been identified by national standards bodies as the primary wavelength reference in the C-band (1530 – 1565nm) while Acetylene ( $^{12}C_2H_2$ ) is recognized as a primary wavelength reference in the 1510 to 1540nm band.

---