

[All Products](#) / [Cameras](#) / [USB Cameras](#) / [IDS Imaging uEye+ CP/XCP/SE USB3 Cameras](#)

[See all 106 Products in Family](#)

IDS U3-3890SE-M-GL, USB 3.0, 1/1.7" Monochrome Camera

See More by [IDS Imaging Development Systems](#)



IDS Imaging uEye+ USB3 Camera, SE Model (Front)



Stock **#24-139** [CONTACT US](#)

-1+

S\$971⁵⁰

ADD TO CART

Volume Pricing	
Qty 1+	S\$971.50 each
Need More?	Request Quote

Product Downloads

SPECIFICATIONS

General

Type:
Monochrome Camera

Model Number:

U3-3890SE-M-GL	
IDS Imaging Development Systems	Manufacturer:
uEye+ SE	Camera Series:
Monochrome	Spectrum:
Physical & Mechanical Properties	
34 x 44 x 47 (excludes connectors and lens mount)	Dimensions (mm):
110	Weight (g):
Full	Housing:
Sensor	
128MB	Image Buffer:
1/1.7"	Sensor Format:
12.00	Resolution (Megapixels):
33.00	Frame Rate (fps):
4,000 x 3,000	Pixels (H x V):
1.85 x 1.85	Pixel Size, H x V (µm):
7.4 x 5.55	Sensing Area, H x V (mm):
Sony IMX226	Imaging Sensor:
Progressive Scan CMOS	Type of Sensor:
Rolling	Shutter Type:
12 bit	Pixel Depth:
0.13ms - 609ms	Exposure Time:
68.00	Dynamic Range (dB):
USB3 Vision	Machine Vision Standard:
Electrical	
2 - 3.6	Power Consumption (W):
Hardware & Interface Connectivity	
USB 3.0	Interface:
USB Type-C, screwable	Connector:
Power over USB	Power Supply:
2 Flash Output, 2 Trigger Input, 2 GPIO, 1 Voltage Output, 1 Ground	GPIOs:
Hardware Trigger (GPIO); Software Trigger	Synchronization:
Back Panel	Interface Port Orientation:
8-pin Hirose connector (HR25-7TR-8PA(73))	GPIO Connector Type:
Threading & Mounting	
C-Mbunt	Mount:
1/4-20 with Tripod Mount Adapter	Mounting Threads:
Environmental & Durability Factors	
	Operating Temperature (°C):

0 to +55	
	Storage Temperature (°C):
-20 to +60	

Regulatory Compliance

Exempt

RoHS 2015:

View

Certificate of Conformance:

Contains SVHC(s)

REACH 241:

PRODUCT DETAILS

- Standard (SE), Compact (CP), and Ultra Compact (XCP) Housing Options Available
- C-Mount with Large Format CMOS Sensors up to 1.1"
- Up to 20.44MP Resolution with Framerrates up to 396fps

IDS Imaging uEye CP/XCP/SE USB3 Cameras utilize [IDS Imaging's peak SDK platform](#) that supports GeniCam and USB3 Vision standards for easy software development and integration. The CP cameras are the industry standard size of 29 x 29 x 29mm and work for almost any application. The XCP cameras have an ultra-compact size of 29 x 29 x 17mm and are an excellent option for price-sensitive, single-camera applications. The SE cameras have a larger housing size of 34 x 44 x 47mm to allow for exceptional heat management and are ideal for noise and heat-sensitive applications. IDS Imaging uEye CP/XCP/SE USB3 Cameras are ideal for manufacturing, industrial, and automation applications.