

IR M77 x 0.75 Mounted Machine Vision Filter



Mounted Machine Vision Filters

Stock #21-408 3-5 DAYS

⊖ 1 ⊕ **S\$516.20**

ADD TO CART

Qty 1-9

S\$516.20

Qty 10+

S\$490.68

Volume Pricing

[Request Quote](#)

Get Product Downloads

Blocking Wavelength Range (nm):
200-770

Clear Aperture CA (mm):
73.00

Coating:
Hard Coated

Filter Thread:
M77 x0.75

Color:
IR

Center Wavelength CWL (nm):
850.00

Construction:
Mounted in Black Anodized Ring

Full Width-Half Max FWHM (nm):
160.00

Mount Thickness (mm):
6.0

Mount Thickness Including Threads (mm):
8.3

Outer Diameter (mm):
80.00

Substrate Thickness (mm):
1.3

Type:
Mounted Imaging Filter

Minimum Transmission (%):
≥85

Regulatory Compliance

RoHS:
[Exempt](#)

Certificate of Conformance:
[View](#)
