

JAI Fusion, 3200D-10GE, 1/1.8" 3.2MP, GigE Multispectral Camera



Stock #29-170 **2 In Stock**

S\$7,420⁰⁰

ADD TO CART

Volume Pricing

Qty 1+	S\$7,420.00 each
Need More?	Request Quote

Product Downloads

Multispectral

Spectrum:

General

Multispectral Camera

Type:

FS-3200D-10GE

Model Number:

JAI

Manufacturer:

Fusion

Camera Series:

Physical & Mechanical Properties

62 x 62 x 86.5
Dimensions (mm):

270
Weight (g):

Full
Housing:

Sensor

1/1.8"
Sensor Format:

3.20
Resolution (Megapixels):

123.00
Frame Rate (fps):

2,048 x 1,536
Pixels (H x V):

3.45 x 3.45
Pixel Size, H x V (µm):

7.1 x 5.3
Sensing Area, H x V (mm):

Sony IMX252
Imaging Sensor:

2 CMOS (Vis/NIR)
Type of Sensor:

Global
Shutter Type:

8/10/12 Bit
Pixel Depth:

GigE Vision
Machine Vision Standard:

Electrical

10.4
Power Consumption (W):

Hardware & Interface Connectivity

GigE (POE)
Interface:

RJ45 with Screw Locks
Connector:

Power Supply:
Power Supply Required and Sold Separately.
USA: #29-172
Europe: #29-172
Japan: #29-172
Korea: Not Available
China: Not Available

Hardware Trigger (GPIO) or Software Trigger
Synchronization:

Back Panel
Interface Port Orientation:

12-pin Hirose
GPIO Connector Type:

Threading & Mounting

C-Mount
Mount:

Environmental & Durability Factors

-5 to +45
Operating Temperature (°C):

-25 to +60
Storage Temperature (°C):

Regulatory Compliance

[View](#)
Certificate of Conformance:

Product Details

- Multispectral Camera Designed with Multiple Sensors
- Designed for 400 – 670nm and 740 – 1000nm Wavelengths
- Backwards Compatible 10GigE Interface

JAI® Fusion Series Cameras are designed to image multiple wavebands at once, allowing for a more flexible imaging experience. Utilizing a prism as the camera input, the incoming light is separated and directed to the multiple

sensors with precision per-pixel alignment, providing excellent resolution of the individual wavebands. With a backwards compatible 10GigE interface, these cameras are easily integrated into existing imaging systems. JA® Fusion Series Cameras have effective wavelength ranges of 400 to 670nm and 740 to 1000nm. These cameras are ideal for applications including surface inspection, NIR fluorescence, life sciences, and intelligent farming.

Note: These cameras require prism-corrected imaging lenses; alternatively, standard imaging lenses with zero rear protrusion can be used with reduced performance. Downloadable software is [available](#) online.
