

Intensity Adjustment Potentiometer for Effilux RGB LED Lights



Intensity Adjustment Potentiometer for Effilux LED Lights



Stock **#15-876** 1 In Stock

-

1

+

S\$530^{.00}

ADD TO CART

Volume Pricing	
Qty 1+	S\$530.00 each
Need More?	Request Quote

Product Downloads


General	
EFFI-DIMMER-3DIM	Model Number:
Accessory	Type of Illumination:
Effilux	Manufacturer:
Hardware & Interface Connectivity	

24	Input Voltage (V):
0-5 or 0-24	Output Voltage (V):
Input/Output Options: Input: M12 connector Output: One M12 Connector (0-5V or 0-24V)	
Regulatory Compliance	
Contains SVHC(s)	Reach 219:
View	Certificate of Conformance:

Product Details

- Direct Access to Optics for Quick, Manual Adjustment of Illumination Cone Angles
 - Included Interchangeable Windows Allows for Easy Adjustment of Light Diffusion
 - Easy to Integrate Linescan Accessory for Linear or Darkfield Lighting
- Effilux Adjustable LED Bar Lights provide versatility by allowing the emission angle of the light to be modified by the user. Various illumination emission angles can be modified by simply removing the LED window that's held in place by screws to access the lens array and adjust the lens array height to one of the three indicated positions. Effilux Adjustable LED Bar Lights include three interchangeable windows: transparent, semi-diffuse, and opaline. By placing the optional polarizer or linescan accessories beneath the transparent window, glare can be eliminated or linear lighting created. The flexibility and ease of user modifications for these bar lights make them ideal for use in many application types.
- Note:** 24V power supply and M12 female to male cable are required. When first powered, these lights start in their Overdriven state with 700% intensity then relax to normal intensity.

3D-Printable Mount Files



Bar or Line Light Configuration

DOWNLOAD
NOW

Designed for use with the [Articulating Arm Mounting Systems](#), these 3D-printed mounts allow easy positioning of lights in brightfield or darkfield setups. The design is based on mounting illumination to ¼-20" breadboards or into 80/20 extrusion systems, but can be adapted based on user needs. Mounts are available for ring, bar, line, and inline spot lights.

Illumination Mbunts for Machine Vision Applications
[Read](#) 



Video

Assembly of 3D Printed Mbunts for Common Illumination Geometries
[Watch](#) 