

JAI Go-X, 8901C-PGE, 1" 8.9MP, GigE Color Camera



Stock #29-151 1 In Stock

-

1

+

S\$2,352^{.00}

ADD TO CART

Volume Pricing	
Qty 1+	S\$2,352.00 each
Need More?	Request Quote

Product Downloads

SPECIFICATIONS

Color

Spectrum:

General

Color Camera

Type:

GOX-8901C-PGE

Model Number:

JAI

Manufacturer:

Go-X	Camera Series:
Physical & Mechanical Properties	
29 x29 x51.5	Dimensions (mm):
65	Weight (g):
Full	Housing:
Sensor	
1"	Sensor Format:
8.90	Resolution (Megapixels):
12.00	Frame Rate (fps):
4,096 x2,160	Pixels (H x V):
3.45 x3.45	Pixel Size, H x V (µm):
14.1 x7.4	Sensing Area, H x V (mm):
Sony IMX267	Imaging Sensor:
Progressive Scan CMOS	Type of Sensor:
Global	Shutter Type:
8/10/12 Bit	Pixel Depth:
GigE Vision	Machine Vision Standard:
Electrical	
3.7	Power Consumption (W):
Hardware & Interface Connectivity	
GigE (PoE)	Interface:
RJ45 with Screw Locks	Connector:
Power Supply: Power Supply Required and Sold Separately. USA: #29-171 Europe: #29-171 Japan: #29-171 Korea: Not Available China: Not Available	
Synchronization: Hardware Trigger (GPIO) or Software Trigger	
Back Panel	Interface Port Orientation:
6-pin Hirose	GPIO Connector Type:
Threading & Mounting	
C-Mbunt	Mount:
Environmental & Durability Factors	
-5 to +45	Operating Temperature (°C):
-25 to +60	Storage Temperature (°C):
Regulatory Compliance	
View	Certificate of Conformance:

PRODUCT DETAILS

- Up to 12.3 MP Resolution

- USB and GigE Versions Available
- Longest Industry Warranty (6 Years)

JAI® Go-X Series Cameras are designed to be compact, industrial grade, reliable cameras with excellent image quality. Featuring industrial grade shock and vibration ratings (80G/10G) as well as excellent thermal dissipation, these cameras are ideal for factory floors and assembly lines. Designed with a variety of capabilities, these cameras are capable of region-of-interest (ROI), blemish compensation with shading correction, and 8, 10, and 12-bit output. JAI® Go-X Series Cameras are available in resolutions ranging from 2.3 to 12.3MP with both USB or Gigabit Ethernet (GigE) outputs. Downloadable software is [available](#) for both GigE and USB options.
