

[See all 77 Products in Family](#)

LightPath 353215 | 4mm Dia., 0.30 NA, BBAR (350-700nm), Molded Aspheric Lens

See More by [Lightpath®](#)



Precision Molded Aspheric Lenses

Stock **#71-004** **20+ In Stock**

-

1

+

S\$166^{.60}

ADD TO CART

Volume Pricing	
Qty 1-10	S\$166.60 each
Qty 11-49	S\$149.80 each
Need More?	Request Quote

Product Downloads

General

Lightpath Lens Code:

355215

Type:

Aspheric Lens

Typical Applications:

Collimate or Focus Laser Light

Physical & Mechanical Properties

4.00 ±0.015	Diameter (mm):
3.5	Clear Aperture CA (mm):
2.284	Edge Thickness ET (mm):
2.80 +/-0.025	Center Thickness CT (mm):

Protective as needed	Bevel:
----------------------	--------

Optical Properties

6.20 @ 520nm	Effective Focal Length EFL (mm):
0.30	Numerical Aperture NA:

H-FK61M	Substrate: ☐
±1	Focal Length Tolerance (%):

520	Aspheric Design Wavelength (nm):
BBAR (350-700nm)	Coating:

R _{avg} ≤0.5% @ 350 - 700nm	Coating Specification:
40-20	Surface Quality:

1.55	f/#:
350 - 700	Wavelength Range (nm):

4.33	Working Distance (mm):
Infinite	Conjugate Distance:

Regulatory Compliance

Compliant	RoHS 2015:
View	Certificate of Conformance:

Compliant	Reach 247:
-----------	------------

Product Details

- Eliminate Spherical Aberration
- Multiple Coating Options Available
- Range of Numerical Apertures

LightPath® Geltech™ Molded Aspheric Lenses are used to eliminate spherical aberration and improve focusing and collimating accuracy in a variety of laser applications. Low NA aspheric lenses are designed to maintain beam shape, while high NA lenses gather all available light to maintain beam power over long distances. LightPath® Geltech™ Molded Aspheric Lenses are ideal for applications including sighting systems, bar code scanners, laser diode-to-fiber coupling, optical data storage, or biomedical lasers.

LASER OPTICS

MADE BY EDMUND OPTICS®

LEARN MORE

Technical Information



