


# Laminated Wratten ND Filter 3.0 OD 48mm Dia



Stock #29-324 **8 In Stock**

1 **S\$245<sup>.00</sup>**

**ADD TO CART**

Volume Pricing	
Qty 1-10	S\$245.00 each
Qty 11-25	S\$197.40 each
Need More?	<a href="#">Request Quote</a>

Product Downloads
<a href="#">EO Spec Sheet</a>

## General

<b>Type:</b> Neutral Density Filter	<b>Note:</b> Supplied with protective film on both sides
-------------------------------------	--

## Physical & Mechanical Properties

<b>Diameter (mm):</b> 48.00 +/- 0.3	
-------------------------------------	--

## Optical Properties

<b>Optical Density OD (Average):</b> 3	<b>Substrate:</b> <sup>ⓘ</sup> Wratten 2 Filter, One-Side Laminated onto PMMA
<b>Coating:</b> Uncoated	<b>Blocking Wavelength Range (nm):</b> 400-700

## Regulatory Compliance

<b>Certificate of Conformance:</b> <a href="#">View</a>	
---	--

## Product Details

- One-Side Laminated for Stability
- Available in 25mm and 48mm Sizes
- Kodak Filter No. 96
- Lightweight Alternative to Traditional Glass ND Filters

PMMA-Laminated Wratten ND Filters are ideal for light attenuation in image-forming optical systems to reduce light intensity across the visible spectrum without altering the spectral profile. The laminated design offers additional stability and durability compared to traditional polyester/gelatin filters while remaining a lightweight alternative to traditional glass ND filters. These ND filters are available in 25mm or 48mm diameters and a thickness of 0.6mm. PMMA-Laminated Wratten ND Filters are uncoated and feature a blocking wavelength of 400 - 700nm with OD options of 0.1, 0.3, 0.5, 1.0, 2.0, and 3.0.