

[See all 12 Products in Family](#)

Laser Detection Card UV



Laser Detection Card UV

Stock **#55-214** 11 In Stock

-

1

+

S\$151^{.20}

ADD TO CART

Volume Pricing	
Qty 1-5	S\$151.20 each
Qty 6-24	S\$144.20 each
Need More?	Request Quote

Product Downloads

General

Type:

Card

Typical Applications:

HeCd, Ar-Ion, tripled Nd:YAG, etc.

Physical & Mechanical Properties

Dimensions (mm):

86 x 54

Size of Active Area (mm):

42 x 23

Optical Properties

UV	Wavelength:
Yellow (580nm), Broadband (490 - 700nm)	Emission Color:
250 - 550nm	Stimulation Range:
<8 W/cm ² @ 337nm, 4ns, 20Hz <40 W/cm ² @ 337nm, 4ns, 1Hz	Minimum Stimulation, Pulsed:

Electrical

6 s - 4 min (dependent on ambient light)	Persistence (Stimulation Removed):
<1 nW/cm ² @ 365nm & 450nm	Minimum Stimulation, Continuous:
100 W/cm ² @ 512nm	Maximum Stimulation, Continuous:
130 MW/cm ² @ 337nm, 4ns 60 MW/cm ² @ 1064nm, 7ns	Maximum Stimulation, Single Pulse:

Regulatory Compliance

Compliant	Reach 191:
Compliant	RoHS 2015:
View	Certificate of Conformance:

Product Details

• Full Spectrum Coverage: UV, VS, IR Series


• 3 Mounted Formats Have Safe, Non-reflective Encapsulation

• Unique, No Pre-charge for IR Detection and No Fading During Use

• Flexibility for Either Transmission or Reflective Viewing





Laser Detection Products offer UV, visible, and IR laser users' greater performance and safety. They reduce problems associated with beam visualization, profiling, and alignment in many applications. Each range is available in three formats. Laser Detection Products' laminated credit card style is for low-power sources and reflective viewing only. The 25mm disk and clip-on wand style is used when frequent component positioning is required. The removable disk is positional at an optics location to enable precise alignment, while the wand format permits handling into the beam path. The optical bench-mountable head format has a large active area and ¼-20 threaded mounting for standard English post/post holder integration.

Technical Information



UV Detection Products

Laser Detection Products				
	UV	VS	IR	NIR
Stimulation Range	250 - 550nm	Band 1: 400 - 640nm	Band 1: 790 - 840nm	700 - 1400nm
		Band 2: 800 - 1700nm	Band 2: 870 - 1070nm	
			Band 3: 1550nm	
Typical Applications	HeCd, Ar-Ion, tripled Nd:YAG, etc.	Ar-Ion, HeNe, HeCd, Nd:YAG, etc.	808nm, 820nm, 830nm, 880nm, 960 - 980nm Laser Diodes, Nd:YAG, 1550nm telecommunications	Nd:YAG, Fiber Laser
Emission Color	Yellow (580nm), Broadband (490nm - 700nm)	Orange/Red (655nm), Broadband (600 - 730nm)	Green (550nm), other peaks at Red (673nm) and Blue (400nm)	Orange/Red (655nm)

Persistence (Stimulation Removed)	6 s - 4 mins (dependent on ambient light)	Visible: 0.5 - 3 s (dependent on ambient light) IR: <0.5 s	800µs	<50 ms
Continuous (Minimum Stimulation)*	<1nW/cm ² @ 450nm & 365nm	<1nW/cm ² @ 450nm <25µW/cm ² @ 950nm	<2µW/cm ² @ 808nm <175 nW/cm ² @ 960nm <100µW/cm ² @ 1550nm	8µW/cm ² @ 1064nm
Pulsed (Minimum Stimulation)*	<8W/cm ² @ 337nm, 4ns, 20Hz, <40W/cm ² @ 337nm, 4ns, 1Hz	2 kW/cm ² @ 1064nm, 7ns, 10Hz	250 kW/cm ² @ 1064nm, 7ns, 10Hz	N/A
Continuous (Maximum Stimulation)	100W/cm ² @ 512nm (all formats)	100W/cm ² @ 512nm (all formats)	100W/cm ² (all formats)	100W/cm ² @ 1064nm (estimated)
Single Pulse (Maximum Stimulation)	130MW/cm ² @ 337nm, 4ns (card only) 850MW/cm ² @ 337nm, 4ns (other formats) 60MW/cm ² @ 1064nm, 7ns (all formats)	130MW/cm ² @ 337nm, 4ns (card only) 850MW/cm ² @ 337nm, 4ns (other formats) 60MW/cm ² @ 1064nm, 7ns (all formats)	35MW/cm ² @ 1064nm, 7ns (all formats)	35MW/cm ² @1064nm, 7ns (estimated)
				

*Measured in darkened conditions