


Laser Safety Window LS15 TRI 100 x 200mm



Laser Safety Windows

Stock **#29-380** **1 In Stock**

-

1

+

S\$181²⁵

ADD TO CART

Volume Pricing	
Qty 1-9	S\$181.25 each
Qty 10+	S\$162.40 each
Need More?	Request Quote

Product Downloads

SPECIFICATIONS

General

EN 207/208 Ratings:

D LB7 and IR LB4 @ 180-315nm
DIRMLB5 @ 315-400nm
D LB5 and IRMLB6 @ 400-534nm
DIRMLB5 @ 720-770nm and 850-1,080nm
D LB5

IR LB7 and MLB7Y @ 750-765nm and 980-1,065nm DIRMLB4 @ 770-850nm	
Polymer	Filter Material:
LS15	Filter:
Physical & Mechanical Properties	
100 x 200	Dimensions (mm):
3.00	Thickness (mm):
Optical Properties	
>7 @ 180 - 534nm >5 @ 720 - 770nm >7 @ 750 - 760nm >4 @ 770 - 850nm >5 @ 850 - 1080nm >7 @ 980 - 1064nm	Optical Density OD (Average):
Amber	Color:
22	Visible Light Transmission VLT (%):
Regulatory Compliance	
View	Certificate of Conformance:

PRODUCT DETAILS

- CE Certified Laser Radiation Protection
- Available for UV, VIS, and NIR Wavelengths
- 200mm x 100mm Size Ideal for Small Enclosures
- 304.8mm x 304.8mm Sizes Also Available

Laser Safety Windows feature high optical density in a specified wavelength range across the UV, VIS, and NIR spectra. Made from acrylic and polycarbonate, these laser safety windows are CE certified to protect against laser radiation. These windows are available in 200 x 100mm for easy integration into small equipment doors, windows, and enclosures. 304.8 x 304.8mm sizes are also available. Laser Safety Windows are ideal for blocking laser radiation while providing safe viewing of laser environments in materials processing, manufacturing, and laboratory applications featuring Nd:YAG, CO₂, fiber, and other laser sources.

Warning: Because of the potential for eye damage, the degree of protection required in each circumstance should be determined by the Laser Safety Officer, the industrial hygienist, or the individual responsible for the safety program.