


# Optotune Low Dispersion, VIS Coated, Electrically Focus Tunable Lens | EL-10-30-TC-VIS-12D

See More by [Optotune](#)



Stock **#34-970** 3-5 DAYS

- 1 +

**S\$906.25**

ADD TO CART

|                  |
|------------------|
| Qty 1+           |
| <b>S\$906.25</b> |

|                               |
|-------------------------------|
| Volume Pricing                |
| <a href="#">Request Quote</a> |

|                       |
|-----------------------|
| Get Product Downloads |
|-----------------------|

**Substrate:** ☐ Low Dispersion Polymer

**Coating:** BBAR (400-700nm)

**Type:** Specialty Lens

**Wavelength Range (nm):** 400 - 700

|                                                                                                |
|------------------------------------------------------------------------------------------------|
| <b>Abbe Number (v<sub>d</sub>):</b><br>100.00                                                  |
| <b>Clear Aperture CA (mm):</b><br>10.0                                                         |
| <b>Current (mA):</b><br>0 - 250, 400 abs. max                                                  |
| <b>Focus Range:</b><br>+8.3 to +20 diopter<br>+55 to +120mm                                    |
| <b>Index of Refraction n<sub>d</sub>:</b><br>1.300                                             |
| <b>Lifecycles:</b><br>>1,000,000,000                                                           |
| <b>Model Number:</b><br>EL-10-30-TC-VIS-12D                                                    |
| <b>Outer Diameter (mm):</b><br>30.0                                                            |
| <b>Power Consumption (W):</b><br>0 - 0.9 (0 - 2 abs. max)                                      |
| <b>Response Time (ms):</b><br>2.5 (10%-90% step)                                               |
| <b>Thickness (mm):</b><br>10.70                                                                |
| <b>Transmitted Wavefront Error, RMS:</b><br>Vertical: 0.2λ @ 525nm<br>Horizontal: 0.5λ @ 525nm |
| <b>Damage Threshold, By Design:</b> <div></div><br>10 kW/cm <sup>2</sup> @ 1064nm              |

Regulatory Compliance

|                                                            |
|------------------------------------------------------------|
| <b>RoHS:</b><br><a href="#">Compliant</a>                  |
| <b>Certificate of Conformance:</b><br><a href="#">View</a> |