

LightPath 353215 | 4mm Dia., 0.30 NA, BBAR (350-700nm), Molded Aspheric Lens

See More by [Lightpath®](#)



Precision Molded Aspheric Lenses

Stock **#71-004** 20+ In Stock

-

1

+

S\$166^{.60}

ADD TO CART

Volume Pricing	
Qty 1-10	S\$166.60 each
Qty 11-49	S\$149.80 each
Need More?	Request Quote

Product Downloads

SPECIFICATIONS

General


355215	Lightpath Lens Code:
Aspheric Lens	Type:

Typical Applications: Collimate or Focus Laser Light	
Physical & Mechanical Properties	
Diameter (mm):	4.00 ±0.015
Clear Aperture CA (mm):	3.5
Edge Thickness ET (mm):	2.284
Center Thickness CT (mm):	2.80 +/-0.025
Bevel:	Protective as needed
Optical Properties	
Effective Focal Length EFL (mm):	6.20 @520nm
Numerical Aperture NA:	0.30
Substrate: 	H-FK61M
Focal Length Tolerance (%):	±1
Aspheric Design Wavelength (nm):	520
Coating:	BBAR (350-700nm)
Coating Specification:	R _{avg} ≤0.5% @ 350 - 700nm
Surface Quality:	40-20
f/#:	1.55
Wavelength Range (nm):	350 - 700
Working Distance (mm):	4.33
Conjugate Distance:	Infinite
Regulatory Compliance	
RoHS 2015:	Compliant
Certificate of Conformance:	View
Reach 247:	Compliant

PRODUCT DETAILS

- Eliminate Spherical Aberration
- Multiple Coating Options Available
- Range of Numerical Apertures

LightPath® Geltech™ Molded Aspheric Lenses are used to eliminate spherical aberration and improve focusing and collimating accuracy in a variety of laser applications. Low NA aspheric lenses are designed to maintain beam shape, while high NA lenses gather all available light to maintain beam power over long distances. LightPath® Geltech™ Molded Aspheric Lenses are ideal for applications including sighting systems, bar code scanners, laser diode-to-fiber coupling, optical data storage, or biomedical lasers.



TECHNICAL INFORMATION

