

[See all 77 Products in Family](#)

LightPath 355625 | 5.585mm Dia., 0.55 NA, BBAR (1050-1600nm), Molded Aspheric Lens

See More by [Lightpath®](#)



Precision Molded Aspheric Lenses

Stock **#16-701** **20+ In Stock**

-

1

+

S\$119^{.00}

ADD TO CART

Volume Pricing	
Qty 1-10	S\$119.00 each
Qty 11-49	S\$107.10 each
Need More?	Request Quote

Product Downloads

General

Lightpath Lens Code:

355625

Type:

Aspheric Lens

Typical Applications:

Collimate or Focus Laser Light

Physical & Mechanical Properties

5.59 ±0.015	Diameter (mm):
4.6	Clear Aperture CA (mm):
2.73	Edge Thickness ET (mm):
3.70 ±0.03	Center Thickness CT (mm):

Protective as needed	Bevel:
----------------------	--------

Optical Properties

4.13 @ 447nm	Effective Focal Length EFL (mm):
0.55	Numerical Aperture NA:

D-ZLaF52LA	Substrate: □
±1	Focal Length Tolerance (%):

447	Aspheric Design Wavelength (nm):
BBAR (1050-1600nm)	Coating:

R _{abs} <1.0% @ 1050 - 1600nm	Coating Specification:
40-20	Surface Quality:

0.91	f/#:
1050 - 1600	Wavelength Range (nm):

2.2	Working Distance (mm):
Infinite	Conjugate Distance:

<0.200	Transmitted Wavefront Error (λ, RMS):
--------	---------------------------------------

Environmental & Durability Factors

≤200	Operating Temperature (°C):
------	-----------------------------


Regulatory Compliance

Compliant	RoHS 2015:
View	Certificate of Conformance:
Compliant	Reach 247:

Product Details

- Eliminate Spherical Aberration
- Multiple Coating Options Available
- Range of Numerical Apertures

LightPath® Geltech™ Molded Aspheric Lenses are used to eliminate spherical aberration and improve focusing and collimating accuracy in a variety of laser applications. Low NA aspheric lenses are designed to maintain beam shape, while high NA lenses gather all available light to maintain beam power over long distances. LightPath® Geltech™ Molded Aspheric Lenses are ideal for applications including sighting systems, bar code scanners, laser diode-to-fiber coupling, optical data storage, or biomedical lasers.



Technical Information



;