

Lightpath 7100346 | 24mm FL, f/1.2, Thermal Imaging Lens Assembly

See More by [Lightpath®](#)



Stock #15-693 CLEARANCE 3-5 DAYS

-

1

+

S\$353.73

ADD TO CART

Qty 1+

S\$353.73

Volume Pricing

[Request Quote](#)

Get Product Downloads

Effective Focal Length EFL (mm):
24.00

Substrate: ☐
Black Diamond™ BD-6

f/#:
1.2

Coating:
BBAR (8000-12000nm)

Wavelength Range (nm):
8000 - 12000

Clear Aperture CA (mm): 20.00
Coating Specification: R _{avg} <0.75% @ 8000 - 12,000nm
Coefficient of Thermal Expansion CTE (10⁻⁶/°C): 22.5
Compatible Window: Thickness: 0.70mm Material: Si
Construction: Matte Black Anodized Aluminum Housing
Index of Refraction n_d @ 10μm: 2.7816
Index of Refraction n_d @ 14μm: 2.7683
Index of Refraction n_d @ 4μm: 2.7978
Length (mm): 26.50
Lightpath Lens Code: 7100346
Mounting Threads: M25 x 0.5
Thermo-optic coefficient dn/dT: 30.5 x 10 ⁻⁶ @ 10μm
Working Distance (mm): 10.00
Front Diameter (mm): 27.00
Thread Length (mm): 5.00
Recommended Detector Format (H x V/Pixel Size): 640 x 480 / 17μm

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 233: Compliant