

[See all 36 Products in Family](#)

M2420, 2/3" Monochrome, DALSA Genie Nano GigE PoE Camera

See More by [Teledyne DALSA](#)



Teledyne DALSA Genie™ Nano GigE Cameras



Stock **#34-962** **3 In Stock**

[Similar Cameras](#)

-

1

+

S\$1,435⁰⁰

ADD TO CART

Volume Pricing	
Qty 1+	S\$1,435.00 each
Need More?	Request Quote

Product Downloads

SPECIFICATIONS

Spectrum:
Monochrome

General

Type:
Monochrome Camera

G3-GM1 1-M2420	Model Number:
Teledyne DALSA	Manufacturer:
Genie Nano-1GigE	Camera Series:
Windows, Linux, or 3rd party GenICam complaint SDK	Software:
Physical & Mechanical Properties	
40.6 x 29.0 x 44.0 (includes connectors and lens mount)	Dimensions (mm):
46	Weight (g):
Full	Housing:
Sensor	
90MB	Image Buffer:
2/3"	Sensor Format:
5.00	Resolution (Megapixels):
23.80	Frame Rate (fps):
35.00	Frame Rate - Burst Mode (fps):
2,448 x 2,048	Pixels (H x V):
3.45 x 3.45	Pixel Size, H x V (µm):
8.45 x 7.07	Sensing Area, H x V (mm):
Sony IMX264	Imaging Sensor:
Progressive Scan CMOS	Type of Sensor:
Global	Shutter Type:
8/12 bit	Pixel Depth:
Programmable or via external trigger	Exposure Time:
76.4	Dynamic Range (dB):
GigE Vision v1.2	Machine Vision Standard:
Electrical	
3.6 - 4.6 (12VDC External Power Supply) 4.0 - 4.9 (PoE)	Power Consumption (W):
Hardware & Interface Connectivity	
GigE (PoE)	Interface:
GigE, RJ45 with Screw Locks	Connector:
Power over Ethernet (PoE) or via GPIO	Power Supply:
2 digital input, 2 digital output	GPIOs:
Hardware Trigger (GPIO), Software Trigger, Free-Run, or PTP (IEEE 1588)	Synchronization:
Back Panel	Interface Port Orientation:
10-pin Samtec	GPIO Connector Type:
2 opto-isolated inputs, 2 opto-insolated outputs	Ports:
Threading & Mounting	

C-Mount	Mount:
1/4-20 with Tripod Mount Adapter	Mounting Threads: #34-966
Environmental & Durability Factors	
-20 to +60	Operating Temperature (°C):
-40 to +80	Storage Temperature (°C):
Regulatory Compliance	
Compliant	REACH 201:
View	Certificate of Conformance:

PRODUCT DETAILS

- TurboDrive™ Technology Achieve Frame Rate up to 800 fps
- Compact, Lightweight, Robust All Metal Body
- Global Electronic Shutter with Exposure Control and Advanced Feature Set



Teledyne DALSA Genie™ Nano GigE Cameras are available in a range of Sony Pregius and On Semiconductor CMOS sensors. These GigE PoE cameras provide high speed, low noise, and global electronic shutters. The proprietary TurboDrive™ technology allows the Genie™ Nano to exceed standard frame rates, delivering up to 800 fps while retaining full image quality. These cameras come with a host of advanced feature set such as multi ROI windows and Burst Acquisition, which utilizes onboard memory buffer to achieve even faster frame rates.* Teledyne DALSA Genie™ Nano GigE Cameras are packaged in compact and robust all metal housing, making them ideal for electronics inspection, industrial metrology, and Intelligent Traffic Systems (ITS) applications.

Note: Frame rates achievable through TurboDrive™ or Burst Acquisition could vary with factors such as image quality and resolution.

Sapera LT is a free image acquisition and control software development toolkit (SDK) for Teledyne DALSA'S 1D cameras / 2D cameras / 3D Laser Profiler cameras and frame grabbers. Hardware independent in nature, Sapera LT offers a rich development ecosystem for machine vision OEMs and system integrators. Sapera LT supports image acquisition from cameras and frame grabbers based on machine vision standards including GigE Vision™, CameraLink®, CameraLink HS™, CoaXpress®, and USB3 Vision™.