

[See all 36 Products in Family](#)

# M1280, 1/2" NIR, Teledyne DALSA Genie Nano GigE PoE Camera

See More by [Teledyne DALSA](#)



Teledyne DALSA Genie™ Nano GigE Cameras



Stock #14-675 [CONTACT US](#)

⊖ 1 ⊕ **\$826<sup>00</sup>**

**ADD TO CART**

Volume Pricing	
Qty 1+	<b>\$826.00</b> each
Need More?	<a href="#">Request Quote</a>

## Product Downloads

NIR **Spectrum:**

## General

NIR Camera **Type:**

G3-GM12-M1280 **Model Number:**

**Manufacturer:**

Teledyne DALSA

**Camera Series:**

Genie Nano-1GigE

## Physical & Mechanical Properties

**Dimensions (mm):**

40.6 x 29.0 x 44.0 (includes connectors and lens mount)

**Weight (g):**

46

**Housing:**

Full

## Sensor

**Image Buffer:**

90MB

**Sensor Format:**

1/2"

**Resolution (Megapixels):**

1.30

**Frame Rate (fps):**

92.00

**Frame Rate - Burst Mode (fps):**

213.00

**Pixels (H x V):**

1,280 x 1,024

**Pixel Size, H x V (µm):**

4.8 x 4.8

**Sensing Area, H x V (mm):**

6.14 x 4.92

**Imaging Sensor:**

ON Semi PYTHON 1300

**Type of Sensor:**

Progressive Scan CMOS

**Shutter Type:**

Global

**Pixel Depth:**

8/10 bit

**Exposure Time:**

Programmable or via external trigger

**Dynamic Range (dB):**

62.1

**Machine Vision Standard:**

GigE Vision v1.2

## Electrical

**Power Consumption (W):**

3.6 - 4.6 (12VDC External Power Supply)  
4.0 - 4.9 (PoE)

## Hardware & Interface Connectivity

**Interface:**

GigE (PoE)

**Connector:**

GigE, RJ45 with Screw Locks

**Power Supply:**

Power over Ethernet (PoE) or via GPIO

**GPIOs:**

2 digital input, 2 digital output

**Synchronization:**

Hardware Trigger (GPIO), Software Trigger, Free-Run, or PTP (IEEE 1588)

**Interface Port Orientation:**

Back Panel

**GPIO Connector Type:**

10-pin Samtec

## Threading & Mounting

**Mount:**

C-Mount

**Mounting Threads:**

1/4-20 with Tripod Mount Adapter [#34-966](#)

## Environmental & Durability Factors

**Operating Temperature (°C):**

-20 to +60

-40 to +80      **Storage Temperature (°C):**

## Regulatory Compliance

[View](#)      **Certificate of Conformance:**

## Product Details

- TurboDrive™ Technology Achieve Frame Rate up to 800 fps
- Compact, Lightweight, Robust All Metal Body
- Global Electronic Shutter with Exposure Control and Advanced Feature Set



Teledyne DALSA Genie™ Nano GigE Cameras are available in a range of Sony Pregius and On Semiconductor CMOS sensors. These GigE PoE cameras provide high speed, low noise, and global electronic shutters. The proprietary TurboDrive™ technology allows the Genie™ Nano to exceed standard frame rates, delivering up to 800 fps while retaining full image quality. These cameras come with a host of advanced feature set such as multi ROI windows and Burst Acquisition, which utilizes onboard memory buffer to achieve even faster frame rates.\* Teledyne DALSA Genie™ Nano GigE Cameras are packaged in compact and robust all metal housing, making them ideal for electronics inspection, industrial metrology, and Intelligent Traffic Systems (ITS) applications.

**Note:** Frame rates achievable through TurboDrive™ or Burst Acquisition could vary with factors such as image quality and resolution.

**Sapera LT** is a free image acquisition and control software development toolkit (SDK) for Teledyne DALSA'S 1D cameras / 2D cameras / 3D Laser Profiler cameras and frame grabbers. Hardware independent in nature, Sapera LT offers a rich development ecosystem for machine vision OEMs and system integrators. Sapera LT supports image acquisition from cameras and frame grabbers based on machine vision standards including GigE Vision™, CameraLink®, CameraLink HS™, CoaXpress®, and USB3 Vision™.