

MF12x1 to SM1 and SM05 Thread Adapter



MF12x1 to SM1 and SM05 Thread Adapter

Stock **#26-742** **1 In Stock**

-

1

+

S\$97^{ea}

ADD TO CART

Volume Pricing	
Qty 1+	S\$97.88 each
Need More?	Request Quote

Product Downloads

SPECIFICATIONS

Regulatory Compliance

[View](#)

Certificate of Conformance:

PRODUCT DETAILS

- Two Color Si-InGaAs Chip for 320 – 1700nm Wavelength Range
- Embedded 24-Bit Analog-to-Digital Converter
- Digital USB Connection and Two Analog BNC Connections

NIREOS SPIDER High-Dynamic Range VIS-SVMR Photodetector is a broadband, amplified Si-InGaAs photodetector that allows for analog or digital connection and enables rapid development of high-performance sensing and spectroscopy solutions suitable in industrial, laboratory, and research environments. Featuring a two-color Si and InGaAs chip, this photodetector allows straightforward beam alignment and achieves a wide spectral response ranging from 320 - 1700nm. With an embedded 24-bit analog-to-digital converter (ADC), the Si and InGaAs analog outputs are simultaneously digitized with adjustable sampling rates from 0.5 to 120kSPS via USB connection. NIREOS SPIDER High-Dynamic Range VIS-SVMR Photodetector's Si and InGaAs channels are both independently amplified with analog bandwidths up to 56kHz, picowatt sensitivity, and 8 switchable transimpedance gain options ranging from 1.5kΩ to 4.4MΩ. This photodetector comes with a user friendly, plug-and-play software for ease of setup, and features DLLs allowing for programming using .NET based languages such as C++, C#, LabView, Python, and MATLAB.

TECHNICAL INFORMATION

