

[See all 36 Products in Family](#)

M145, 1/2.9" Monochrome, DALSA Genie Nano GigE PoE Camera

See More by [Teledyne DALSA](#)



Teledyne DALSA Genie™ Nano GigE Cameras



Stock **#91-777** NEW **1 In Stock**

- 1 + **S\$712^{.60}**

ADD TO CART

Volume Pricing	
Qty 1+	S\$712.60 each
Need More?	Request Quote

Product Downloads

Monochrome		Spectrum:
General		
Monochrome Camera		Type:
G3-GM10-M1450		Model Number:
		Manufacturer:

Teledyne DALSA	
Genie Nano-1GigE	Camera Series:

Windows, Linux, or 3rd party GenICam compliant SDK	Software:
--	-----------

Physical & Mechanical Properties

40.6 x 29.0 x 44.0 (includes connectors and lens mount)	Dimensions (mm):
47	Weight (g):

Full	Housing:
------	----------

Sensor

90MB	Image Buffer:
1/2.9"	Sensor Format:

1.50	Resolution (Megapixels):
76.00	Frame Rate (fps):

150.00	Frame Rate - Burst Mode (fps):
1,456 x 1,088	Pixels (H x V):

3.45 x 3.45	Pixel Size, H x V (µm):
5.02 x 3.76	Sensing Area, H x V (mm):

Sony IMX273	Imaging Sensor:
Progressive Scan CMOS	Type of Sensor:

Global	Shutter Type:
8/12 bit	Pixel Depth:

Programmable or via external trigger	Exposure Time:
76	Dynamic Range (dB):

GigE Vision v1.2	Machine Vision Standard:
------------------	--------------------------

Electrical

3.6 - 4.6 (12VDC External Power Supply) 4.0 - 4.9 (PoE)	Power Consumption (W):
--	------------------------

Hardware & Interface Connectivity

GigE (PoE)	Interface:
GigE, RJ45 with Screw Locks	Connector:

Power over Ethernet (PoE) or via GPIO	Power Supply:
2 digital input, 2 digital output	GPIOs:

Hardware Trigger (GPIO), Software Trigger, Free-Run, or PTP (IEEE 1588)	Synchronization:
Back Panel	Interface Port Orientation:

10-pin Samtec	GPIO Connector Type:
2 opto-isolated inputs, 2 opto-insolated outputs	Ports:

Threading & Mounting

C-Mount	Mount:
	Mounting Threads:

Environmental & Durability Factors

-20 to +65	Operating Temperature (°C):
-40 to +80	Storage Temperature (°C):

Regulatory Compliance

Exempt	RoHS 2015:
View	Certificate of Conformance:

Product Details

- TurboDrive™ Technology Achieve Frame Rate up to 800 fps
- Compact, Lightweight, Robust All Metal Body
- Global Electronic Shutter with Exposure Control and Advanced Feature Set



Teledyne DALSA Genie™ Nano GigE Cameras are available in a range of Sony Pregius and On Semiconductor CMOS sensors. These GigE PoE cameras provide high speed, low noise, and global electronic shutters. The proprietary TurboDrive™ technology allows the Genie™ Nano to exceed standard frame rates, delivering up to 800 fps while retaining full image quality. These cameras come with a host of advanced feature set such as multi ROI windows and Burst Acquisition, which utilizes onboard memory buffer to achieve even faster frame rates.* Teledyne DALSA Genie™ Nano GigE Cameras are packaged in compact and robust all metal housing, making them ideal for electronics inspection, industrial metrology, and Intelligent Traffic Systems (ITS) applications.

Note: Frame rates achievable through TurboDrive™ or Burst Acquisition could vary with factors such as image quality and resolution.

Sapera LT is a free image acquisition and control software development toolkit (SDK) for Teledyne DALSA'S 1D cameras / 2D cameras / 3D Laser Profiler cameras and frame grabbers. Hardware independent in nature, Sapera LT offers a rich development ecosystem for machine vision OEMs and system integrators. Sapera LT supports image acquisition from cameras and frame grabbers based on machine vision standards including GigE Vision™, CameraLink®, CameraLink HS™, CoaXpress®, and USB3 Vision™.