


Microlens Array 10 x 10mm, 300μm Pitch, 1° Divergence, UV-VIS Coated



Microlens Arrays



Stock #21-148 3-5 DAYS

1

S\$1,167.25

ADD TO CART

Qty 1-10

S\$1,167.25

Qty 11+

S\$1,049.80

Volume Pricing

[Request Quote](#)

Get Product Downloads

Effective Focal Length EFL (mm):
8.70

Substrate: ☐
[Fused Silica](#)

Coating:

UV-MS (250-700nm)
Type: Lens Array
Wavelength Range (nm): 250 - 700
Coating Specification: R _{abs} ≤1.0% @ 350 - 450nm R _{avg} ≤1.5% @ 250 - 700nm
Dimensional Tolerance (mm): ±0.05
Dimensions (mm): 10.0 x 10.0
Divergence Angle (°): ±1
Lens Profile: Spherical
Pitch (μm): 300.00
Pitch Tolerance (μm): ±0.25
Radius R (mm): 4.00
Thickness (mm): 1.20
Thickness Tolerance (mm): ±0.05
Type of Optics: Plano-Convex

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 235: Compliant