

[See all 3 Products in Family](#)

NIST Traceable Longwave Sensor, 335 - 380nm



#88-136 with NIST Traceable Sensor

Stock **#88-139** **1 In Stock**

-

1

+

S\$770⁰⁰

ADD TO CART

Volume Pricing	
Qty 1+	S\$770.00 each
Need More?	Request Quote

Product Downloads

Physical & Mechanical Properties

±5	Accuracy (%):
----	---------------

Optical Properties

335 - 380	Wavelength Range (nm):
365.00	Calibration Wavelength (nm):

Regulatory Compliance

Product Details

- Designed to Detect UV Wavelengths from 250 – 380nm
- NIST Certified Sensors
- 9V Battery Provides up to 120 Hours of Operation
- Requires One NIST Traceable Sensor for Operation

The NIST Certified UV Radiometer is ideal for inspecting ultraviolet light sources in a variety of quality control applications. The NIST Certified UV Radiometer is powered by a standard 9V battery for up to 120 hours of operation. Three NIST certified interchangeable sensors are available to detect a wide range of ultraviolet wavelengths from 250 – 380nm. The NIST Certified UV Radiometer's range switch allows the selection of three intensity ranges.

Note: The UV Radiometer Unit ([#88-136](#)) requires one NIST Traceable Sensor ([#88-137](#), [#88-138](#), or [#88-139](#)) for operation.