

## Narrow SWIR 1450nm C-Mount Bandpass Filter



C-Mount Camera Imaging Filters

Stock **#73-325** [CONTACT US](#)

⊖ 1 ⊕ **S\$560<sup>00</sup>**

**ADD TO CART**

### Volume Pricing

Qty 1-9	<b>S\$560.00</b> each
Qty 10+	<b>S\$532.00</b> each
Need More?	<a href="#">Request Quote</a>

### Product Downloads

### General

SWIR Bandpass Filter **Type:**

### Physical & Mechanical Properties

19.50 **Clear Aperture CA (mm):**

25.40 **Outer Diameter (mm):**

**Construction:**

Mounted in Black Anodized Ring

Substrate Thickness (mm):  
1.00

## Optical Properties

Full Width-Half Max FWHM (nm):  
35.00 +/- 10

Minimum Transmission (%):  
≥90

Coating:  
AR Hard Coated

Color:  
SWIR

Surface Quality:  
40-20

Transmission Wavelength (nm):  
1440 - 1460

## Threading & Mounting

Filter Thread:  
C-Mount

Mount Thickness (mm):  
3.00

## Regulatory Compliance

RoHS 2015:  
[Compliant](#)

Certificate of Conformance:  
[View](#)

Reach 242:  
[Compliant](#)

## Product Details

- Threads Directly between a Lens and any C-Mount Camera
- Narrow UV, VIS and SWIR Bandpass Filters Available
- Recommended for Wide Angle Lenses
- UV Protective Windows Available

C-Mount Camera Imaging Filters feature narrow imaging bandpass filters, covering the UV, VIS, and SWIR spectral ranges and are designed with anti-reflection coatings to minimize light loss and enhance performance. These filters are designed to thread directly into any C-mount camera, between the lens and sensor, to ensure compatibility across devices and are particularly useful in applications with space constraints or lenses without filter threads. A custom installation wrench is included with each filter. C-Mount Camera Imaging Filters achieve high transmission rates, typically exceeding 85%, while maintaining a narrow bandwidth, allowing them to selectively transmit a specific wavelength range. These imaging filters are ideal for applications where precise wavelength selection is crucial for optimal imaging and detection such as; Food & Agricultural Inspection, Densitometry, Remote Sensing, and Security and Surveillance.

**Note:** UV Protective Windows offering low absorption and excellent thermal stability are available for imaging applications between 350 – 1100nm.