

Ocean Optics HRX4 Extended Range High Resolution Spectrometer

See More by [Ocean Optics](#)



Stock #91-560 NEW **1 In Stock**

⊖ 1 ⊕ **S\$10,527⁰⁰**

ADD TO CART

Volume Pricing

| | |
|------------|-------------------------------|
| Qty 1+ | S\$10,527.00 each |
| Need More? | Request Quote |

Product Downloads

General

OceanDirect & OceanView

Software:

3.8 ms – 10 s

Integration Time:

HR-4XR500-25

Model Number:

Note:
Includes manual QR code, software QR code, calibration reports for wavelength and linearity, 1 m USB cable

SMA905 **Input Port Termination:**

Grating:
Ruled Diffraction Grating: 300 Grooves/mm, Blazed @ 500nm

Cross Czerny Turner **Optical Bench:**

Physical & Mechanical Properties

25 **Slit Width (µm):**

0.9306 **Weight (kg):**

148.8 x 106.4 x 48.2 **Dimensions (mm):**

Optical Properties

1.00 **Spectral Resolution (nm):**

190 - 1100 **Wavelength Range (nm):**

Sensor

CCD **Type of Sensor:**

Electrical

Signal to Noise S/N Ratio:
Single Scan @ 10 ms: 250:1
Max per second with High Speed Averaging Mode:
3000:1

Hardware & Interface Connectivity

USB, RS-232 **Computer Interface:**

Threading & Mounting

(3) 2-56 **Mounting Threads:**

Environmental & Durability Factors

0 to +55 **Operating Temperature (°C):**

-30 to +70 **Storage Temperature (°C):**

0.02 nm/°C **Thermal Stability:**

Regulatory Compliance

RoHS 2015:
[Compliant](#)

Certificate of Conformance:
[View](#)

Product Details

- High Resolution Spectrometers for Narrow Peak Identification
- Spectral Ranges Spanning UV-VIS, VIS-NIR, and NIR Wavelengths
- Rapid Acquisition Speed and Excellent Thermal Stability

Ocean Optics HR High Resolution Spectrometers, available in HR2, HR4, and HR6 models, are designed to identify narrow spectral peaks with detailed spectral analysis for applications that require high-resolution solutions. The HR2 spectrometers feature high-resolution performance, fast scan speeds, and excellent thermal stability, providing rapid, real-time results ideal for applications such as plasma monitoring and pharmaceutical analysis. The HR4 spectrometers combine high-resolution spectral analysis with excellent thermal stability, making these models excel in precision-demanding environments such as DNA/RNA analysis, biomedical research, and high-throughput reflection testing. The HR6 spectrometers offer high sensitivity, high resolution, and excellent signal-to-noise ratio (SNR) performance for applications including protein absorbance and emission of broadband sources. The Ocean Optics HR High Resolution Spectrometers include the user-friendly OceanView software system to optimize spectrometer performance, ease system integration, and access data for analysis.