


[See all 41 Products in Family](#)

Olympus LMPLFLN-BD 5X Objective

See More by [Olympus](#)



#86-827

Stock **#86-827** 1 In Stock

-

1

+

S\$2,583^{.00}

ADD TO CART

Volume Pricing	
Qty 1+	S\$2,583.00 each
Need More?	Request Quote

Product Downloads

SPECIFICATIONS

General

1-U2N342

Model Number:

Compatible Tube Lens Focal Length (mm):
Focal Length: 180mm

Microscope Objective


Type:

Infinity Corrected	Style:
Olympus	Manufacturer:
Darkfield Objective	Note:
Physical & Mechanical Properties	
32.00	Diameter (mm):
5.3	Field of View (mm):
30.00	Length excluding Threads (mm):
32	Maximum Diameter (mm):
81	Weight (g):
Optical Properties	
N/A	Compatible Cover Glass Thickness (mm):
36.00	Focal Length FL (mm):
5X	Magnification:
0.13	Numerical Aperture NA:
2.58	Resolving Power (μm):
16.27	Depth of Field (μm):
15.0	Working Distance (mm):
400 - 700	Wavelength Range (nm):
26.5	Field Number (mm):
45	Parfocal Length (mm):
N/A	Immersion Liquid:
Threading & Mounting	
M26 x 36 TPI	Mounting Threads:
Environmental & Durability Factors	
20 - 80%RH with no condensation	Operating Humidity:
Regulatory Compliance	
View	Certificate of Conformance:


PRODUCT DETAILS

- Ideal for Brightfield, DIC, Fluorescence, or Polarization Microscopy
 - Long Working Distances Reduce Risk of Specimen Damage
 - Excellent Transmission from 400 – 700nm
 - Additional [Olympus Infinity Corrected Objectives](#) Available
- Olympus MPlan Fluorite Semi Apochromat Infinity Corrected Objectives are ideal for a range of applications utilizing a variety of illumination methods. Olympus MPlan Fluorite Semi Apochromat Infinity Corrected Objectives offer long working distances to increase specimen safety, in addition to increased contrast for observation. These objectives feature standard pupil positions, which enable the use of multiple [prisms](#) or [polarizers](#) for differential interference contrast (DIC) optical microscopy applications.


TECHNICAL INFORMATION




Typical Transmission



Using Olympus Objectives with C-Mount Cameras



Stock #	Model	A	B	C	D	E	F	G	WD
#88-202	LMPLFLN 5X	22.5	0.3	-	25.4	-	26.0	4.9	22.5
#88-203	LMPLFLN 10X	24.0	1.9	-	15.2	22.4	26.0	4.5	21.0
#88-204	LMPLFLN 20X	33.0	3.7	-	17.0	-	26.0	4.8	12.0
#88-205	LMPLFLN 50X	34.4	4.0	-	18.2	-	26.0	4.9	10.6
#88-206	LMPLFLN 100X	41.6	3.8	0.5	12.5	18.1	26.0	4.7	3.4
#16-880	MPLFLN 1.25X	41.5	-	-	28.6	29.0	30	4.9	3.5
#39-573	MPLFLN 2.5X	34.3	2.7	-	24.5	29.0	30.0	4.9	10.7
#88-332	MPLFLN 5X	25.0	2.5	-	20.9	-	26.0	4.5	20.0
#88-333	MPLFLN 10X	34.0	5.6	-	14.5	-	26.0	4.5	11.0
#23-721	MXPLFLN 20X	42.0	2.63	2.15	9	20.4	26	4.8	3
#23-722	MXPLFLN 50X	42.0	3.4	1.96	10.3	19	26	4.5	3



Stock #	Model	A	B	C	D	E	F	G	WD
#86-827	LMPLFLN-BD 5X	30.0	2.6	3.4	16.2	29.5	32.0	5.0	15.0
#86-828	LMPLFLN-BD 10X	35.0	2.1	2.7	15.5	30.0	32.0	4.5	10.0
#86-829	LMPLFLN-BD 20X	33.0	1.2	0.5	22.0	30.0	32.0	4.5	12.0
#86-830	LMPLFLN-BD 50X	34.4	1.2	1.4	20.7	28.0	32.0	4.8	10.6
#86-831	LMPLFLN-BD 100X	41.7	1.2	4.0	21.0	29.0	32.0	4.7	3.3

