

[See all 2 Products in Family](#)

# Olympus UPLAPO 100X Oil Immersion Objective

See More by [Olympus](#)



#90-690 Olympus UPLAPO 100X oil Immersion Objective

Stock #90-690 **NEW** 1 In Stock

⊖ 1 ⊕ **\$23,478<sup>00</sup>**

**ADD TO CART**

Volume Pricing	
Qty 1+	\$23,478.00 each
Need More?	<a href="#">Request Quote</a>

## Product Downloads

### General

**Model Number:**  
UPLAPO100XOHR

**Compatible Tube Lens Focal Length (mm):**  
Focal Length: 180mm

**Type:**  
Microscope Objective

**Style:**  
Infinity Corrected

**Manufacturer:**

Olympus

Note:

Recommended Immersion Oil [#86-834](#)

## Physical & Mechanical Properties

Field of View (mm):

0.22

Length excluding Threads (mm):

44.77

Maximum Diameter (mm):

31.5

Weight (g):

182

## Optical Properties

Compatible Cover Glass Thickness (mm):

0.13-0.19

Focal Length FL (mm):

1.80

Magnification:

100X

Numerical Aperture NA:

1.50

Resolving Power ( $\mu\text{m}$ ):

0.22

Depth of Field ( $\mu\text{m}$ ):

0.19

Working Distance (mm):

0.12

Field Number (mm):

22

Parfocal Length (mm):

45

Immersion Liquid:

Oil

Entrance Pupil Diameter (mm):

5.40

## Threading & Mounting

Mounting Threads:

RMS / 20.32mm x 36 TPI

## Regulatory Compliance

Certificate of Conformance:

[View](#)

## Product Details

- The First Plan-Corrected Achromat Objectives with NA of 1.50
- Ideal for Total Internal Reflection Fluorescence (TIRF) & SuperResolution Applications
- Enhanced Image Flatness, Light Throughput, and Chromatic Correction

Olympus High Resolution TIRF Plan Achromat Objectives are the first plan-corrected achromat objectives to achieve a numerical aperture of 1.50 using standard oil immersion. These objectives deliver superior image flatness, high light throughput, and exceptional chromatic correction across the visible spectrum. Their high NA enables enhanced resolution and contrast, critical for discerning fine structural details in demanding imaging systems. Olympus High Resolution TIRF Plan Achromat Objectives are optimized for TIRF and super-resolution techniques such as TIRF-RIM (Random Illumination Microscopy), TIRF-SIM (Structured Illumination Microscopy), and STORM (Stochastic Optical Reconstruction Microscopy), providing maximum signal efficiency while minimizing phototoxicity. These objectives are the ideal choice for researchers requiring the highest fidelity in live-cell, membrane, and single-molecule imaging applications.