

Olympus UPLFLN 60X Objective

See More by [Olympus](#)



Olympus UPLFLN 60X Objective

Stock **#86-822** **8 In Stock**

-

1

+

S\$5,579^{.31}

ADD TO CART

Volume Pricing	
Qty 1+	S\$5,579.31 each
Need More?	Request Quote

Product Downloads

SPECIFICATIONS

General

1-U2B5312

Model Number:

Compatible Tube Lens Focal Length (mm):
Focal Length: 180mm

Type:

Microscope Objective	
Infinity Corrected	Style:
Olympus	Manufacturer:
Physical & Mechanical Properties	
0.44	Field of View (mm):
44.70	Length excluding Threads (mm):
31	Maximum Diameter (mm):
156	Weight (g):
Optical Properties	
0.11 - 0.23	Compatible Cover Glass Thickness (mm):
3.00	Focal Length FL (mm):
60X	Magnification:
0.90	Numerical Aperture NA:
0.36	Resolving Power (μm):
0.34	Depth of Field (μm):
0.20	Working Distance (mm):
380 - 900	Wavelength Range (nm):
26.5	Field Number (mm):
45	Parfocal Length (mm):
N/A	Immersion Liquid:
Threading & Mounting	
RMS / 20.32mm x 36 TPI	Mounting Threads:
Regulatory Compliance	
Exempt	RoHS 2015:
View	Certificate of Conformance:
Contains SVHC(s)	Reach 247:



PRODUCT DETAILS

- Ideal for Brightfield, Darkfield, DIC, Fluorescence, or Polarization Microscopy
- Excellent Transmission in the UV
- High Numerical Apertures and Oil Immersion Options Available
- Additional [Olympus Infinity Corrected Objectives](#) Available


Olympus Plan Fluorite Objectives are multi-purpose objectives that utilize advanced multi-coatings to provide excellent flat field images from the UV to NIR. The objectives offer high signal-to-noise ratios, excellent resolution, and high contrast imaging capability. These objectives are ideal for brightfield microscopy or Nomarski differential interference contrast (DIC) observations, in addition to darkfield or fluorescence microscopy, or specific polarization techniques. Olympus Plan Fluorite Objectives are available in 4X up to 100X magnification. High Numerical Apertures and Oil Immersion options are available. Additional [Olympus Infinity Corrected Objectives](#) are also offered.

TECHNICAL INFORMATION

86-822



Using Olympus Objectives with C-Mount Cameras



	Stock #	A	B	C	D	E	F	G
UPLFLN 4X	86-817	27.9	2.8	0.0	18.0	18.0	24.0	4.5
UPLFLN 10X	86-818	34.9	10.1	0.0	13.6	13.6	24.0	4.5
UPLFLN 20X	86-819	42.8	5.3	2.3	9.4	15.8	26.0	4.5

UPLFLN 40X	86-820	44.4	5.1	4.0	8.5	16.0	26.0	4.5
UPLFLN 60X	86-822	44.7	5.2	2.7	8.6	17.0	29.0	4.7
UPLFLN 100X(Oil Immersion)	86-823	44.7	5.5	3.0	7.0	17.2	28.0	4.5

Technical drawing of a microscope objective showing dimensions A, B, C, D, E, F, G, and WD. A is the distance from the mounting flange to the front lens. B is the distance from the mounting flange to the rear lens. C is the distance from the mounting flange to the rear lens. D is the distance from the mounting flange to the rear lens. E is the distance from the mounting flange to the rear lens. F is the distance from the mounting flange to the rear lens. G is the distance from the mounting flange to the rear lens. WD is the working distance. The parfocal length is 45.06 mm. The diameter of the mounting flange is Ø20.32 mm.