

Oryx® ORX-10G-310S9C Color 10GigE

See More by [Teledyne FLIR](#)



ORYX-10G-310S9C



+3

Stock **#20-255** 1 In Stock

-

1

+

S\$9,926⁰⁰

ADD TO CART

Volume Pricing	
Qty 1+	S\$9,926.00 each
Need More?	Request Quote

Note: This item requires accessories for use | [Learn More](#)

Product Downloads

SPECIFICATIONS

Color	Spectrum:
General	
Color Camera	Type:
ORX-10G-310S9C	Model Number:
FLIR	Manufacturer:
Onyx®	Camera Series:
Physical & Mechanical Properties	
60 x60 x 115	Dimensions (mm):
508	Weight (g):
Full	Housing:
Sensor	
240MB	Image Buffer:
APS-C	Sensor Format:
31.00	Resolution (Megapixels):
26.00	Frame Rate (fps):
6,464 x 4,852	Pixels (H x V):
3.45 x 3.45	Pixel Size, H x V (µm):
22.30 x 16.74	Sensing Area, H x V (mm):
Sony IMX342	Imaging Sensor:
Progressive Scan CMOS	Type of Sensor:
Global	Shutter Type:
8/10/12 Bit	Pixel Depth:
39µs - 30s	Exposure Time:
67.17	Dynamic Range (dB):
GigE Vision	Machine Vision Standard:
Electrical	
13.9	Power Consumption (W):
Hardware & Interface Connectivity	
10GigE	Interface:
GigE interface with Screw Locks	Connector:
Power Supply: Power Supply Required and Sold Separately: USA: #19-803 Europe: #19-803 Japan: #19-803 Korea: Not Available China: #19-803	
	GPIOs:

1 opto-isolated input, 1 opto-isolated output, 2 non-isolated bi-directional	
Synchronization: Hardware Trigger (GPIO) or Software Trigger	
Interface Port Orientation: Back Panel	
GPIO Connector Type: 12-pin Hirose (HR10)	
Threading & Mounting	
Mount: F-Mount (With #20-256)	
Mounting Threads: Built-in 1/4-20 Tripod Mount Adapter	
Environmental & Durability Factors	
Operating Temperature (°C): 0 to +50	
Storage Temperature (°C): -30 to +60	
Regulatory Compliance	
Certificate of Conformance: View	

PRODUCT DETAILS

- 10GBASE-T (10GigE) Ethernet Interface
- 3.2 to 31 Megapixel Sony 4th Gen Pregius S Sensors
- Supports 4K60, 12-bit System Integration
- Tripod Adapter Built into Larger Oryx® Models



Teledyne FLIR IIS Oryx 10GigE: High throughput, Award-winning camera designs

Reliably capture images at high speed

The **Oryx 10GigE** camera family supports transfer speeds of up to 10 Gbit/s enabling capture of 4K resolution, 12-bit images at speeds exceeding 60 FPS. Reliable image transfer at high bandwidth is further improved with Myricom bundles and packet resend feature. A range of sensor options offer resolutions from 3.2 Megapixel up to 31 Megapixel. Oryx features include IEEE1588 clock synchronization and full compatibility with several popular third-party software supporting GigE Vision. Oryx's 10GBASE-T interface is a proven and widely deployed standard that provides reliable image transfer at cable lengths over 50 meters on inexpensive CAT6A, and up to 30 meters on CAT5e.

Note: The ORX-10G-310S9 and ORX-10G-245S8 cameras require an F-Mount lens adapter (sold separately).

Features

- Color or monochrome sensors
- Various frame triggering options including up to 8 sets of 2-feature sequencer
- Pixel binning, decimation, ROI
- On camera image processing includes Gamma, LUT, and sharpness

Applications

- Stadium venues
- Site security
- Factory automation
- Traffic monitoring
- Inspection systems