

[See all 21 Products in Family](#)

# Oryx® ORX-10GS-123S6M-C Mono 10GigE

See More by [Teledyne FLIR](#)



ORYX-10G-310S9C



Stock **#19-798** **1 In Stock**

- 1 + **\$6,531<sup>00</sup>**

**ADD TO CART**

Volume Pricing

Qty 1+	<b>\$6,531.00</b> each
Need More?	<a href="#">Request Quote</a>

## Product Downloads

Monochrome **Spectrum:**

### General

Monochrome Camera **Type:**

ORX-10GS-123S6M-C **Model Number:**

FLIR **Manufacturer:**

Oryx® **Camera Series:**

### Physical & Mechanical Properties

60 x 60 x 64 **Dimensions (mm):**

386 **Weight (g):**

Full **Housing:**

### Sensor

240MB **Image Buffer:**

1.1" **Sensor Format:**

12.30 **Resolution (Megapixels):**

68.00 **Frame Rate (fps):**

4,096 x 3,000 **Pixels (H x V):**

3.45 x 3.45 **Pixel Size, H x V (µm):**

14.13 x 10.35 **Sensing Area, H x V (mm):**

Sony IMX253 **Imaging Sensor:**

Progressive Scan CMOS **Type of Sensor:**

Global **Shutter Type:**

8/10/12 Bit **Pixel Depth:**

5µs - 30s **Exposure Time:**

71.3 **Dynamic Range (dB):**

GigE Vision **Machine Vision Standard:**

### Electrical

13 **Power Consumption (W):**

### Hardware & Interface Connectivity

10GigE **Interface:**

GigE interface with Screw Locks **Connector:**

**Power Supply:**  
Power Supply Required and Sold Separately.  
USA: [#19-803](#)  
Europe: [#19-803](#)  
Japan: [#19-803](#)  
Korea: Not Available  
China: [#19-803](#)

**GPIOs:**  
2 opto-isolated inputs, 2 opto-isolated outputs, 2 non-isolated bi-directional

**Synchronization:**  
Hardware Trigger (GPIO) or Software Trigger

**Interface Port Orientation:**

**GPIO Connector Type:**

12-pin Hirose (HR10)

**Threading & Mounting****Mount:**

C-Mount

**Mounting Threads:**1/4-20 with Tripod Mount Adapter [#19-804](#)**Environmental & Durability Factors****Operating Temperature (°C):**

0 to +70

**Storage Temperature (°C):**

-30 to +60

**Regulatory Compliance****Certificate of Conformance:**[View](#)

## Product Details

- 10GBASE-T (10GigE) Ethernet Interface
- 3.2 to 31 Megapixel Sony 4th Gen Pregius S Sensors
- Supports 4K60, 12-bit System Integration
- Tripod Adapter Built into Larger Oryx® Models



Teledyne  
Authorized  
Distributor

**Teledyne FLIR IIS Oryx 10GigE: High throughput, Award-winning camera designs**

Reliably capture images at high speed

The **Oryx 10GigE** camera family supports transfer speeds of up to 10 Gbit/s enabling capture of 4K resolution, 12-bit images at speeds exceeding 60 FPS. Reliable image transfer at high bandwidth is further improved with Myricom bundles and packet resend feature. A range of sensor options offer resolutions from 3.2 Megapixel up to 31 Megapixel.

Oryx features include IEEE1588 clock synchronization and full compatibility with several popular third-party software supporting GigE Vision. Oryx's 10GBASE-T interface is a proven and widely deployed standard that provides reliable image transfer at cable lengths over 50 meters on inexpensive CAT6A, and up to 30 meters on CAT5e.

**Note:** The ORX-10G-310S9 and ORX-10G-245S8 cameras require an F-Mount lens adapter (sold separately).

**Features**

- Color or monochrome sensors
- Various frame triggering options including up to 8 sets of 2-feature sequencer
- Pixel binning, decimation, ROI
- On camera image processing includes Gamma, LUT, and sharpness

**Applications**

- Stadium venues
- Site security
- Factory automation
- Traffic monitoring
- Inspection systems