

[See all 12 Products in Family](#)

Polarization Maintaining High ER Patchcord, FC/APC, 0.12NA, 970-1550nm, 1m



FC/APC Connector

Stock **#25-994** **2 In Stock**

-

1

+

S\$378⁰⁰

ADD TO CART

Volume Pricing	
Qty 1-4	S\$378.00 each
Qty 5-24	S\$341.60 each
Need More?	Request Quote

Product Downloads

General

PM980-XP	Fiber Cable Type:
Aligned to Connector Key	Slow Axis Alignment:

Physical & Mechanical Properties

1 +0.1/-0.0	Length (m):
	Jacket Material:

Ø3 mm Blue PVC Furcation Tubing	
2mm Narrow Key	Key Width:
Optical Properties	
0.12	Numerical Aperture NA:
1064	Alignment Wavelength (nm):
970 - 1550	Wavelength Range (nm):
6.6 ± 0.5µm @ 980nm	Mode Field Diameter (nm):
30dB (Min) 33dB (Typ.)	Extinction Ratio:
Hardware & Interface Connectivity	
FC/APC	Connector:
0.50dB (Max) 0.40dB (Typ.)	Insertion Loss (dB):
60	Loss (dB):
Environmental & Durability Factors	
0 to 70	Operating Temperature (°C):
-45 to 85	Storage Temperature (°C):
Regulatory Compliance	
Compliant	RoHS 2015:
View	Certificate of Conformance:
Compliant	REACH 241:

Product Details

- FC/PC, FC/APC, or Hybrid Terminated Connectors
 - Patchcords for Wavelengths from 970 – 1625nm
 - Extinction Ratios up to 33 dB
 - Ideal for Use with 980, 1064, 1310, and 1550nm IR Lasers
- High Extinction Ratio Polarization Maintaining Fiber Optic Patchcords are available with FC/PC or FC/APC terminated connectors. Hybrid terminated connectors enable users to adapt FC/PC and FC/APC patchcords for compatibility with existing fiber assemblies. When used at the fiber specific alignment wavelength, these fiber patchcords provide extinction ratios between 30 – 33 dB to better maintain input polarization. High Extinction Ratio Polarization Maintaining Fiber Optic Patchcords are ideal for applications including telecommunications, interferometry, and quantum key distribution. Each connector is engraved with the fiber type for easy integration and identification.

Custom

Edmund Optics offers comprehensive custom manufacturing services for optical and imaging components tailored to your specific application requirements. Whether in the prototyping phase or preparing for full-scale production, we provide flexible solutions to meet your needs. Our experienced engineers are here to assist—from concept to completion.

Our capabilities include:

- Custom dimensions, materials, coatings, and more
 - High-precision surface quality and flatness
 - Tight tolerances and complex geometries
 - Scalable production—from prototype to volume
- Learn more about our [custom manufacturing capabilities](#) or submit an inquiry [here](#).