

Polarization Maintaining Optical Fiber, PANDA, 770-1100nm, 10m



Stock **#72-905** 3 In Stock

-

1

+

S\$322<sup>.00</sup>

ADD TO CART

| Volume Pricing |                               |
|----------------|-------------------------------|
| Qty 1-4        | S\$322.00 each                |
| Qty 5-24       | S\$289.80 each                |
| Need More?     | <a href="#">Request Quote</a> |

Product Downloads

SPECIFICATIONS

General

Type:  
PM

Physical & Mechanical Properties

Cladding Diameter (μm):

|                       |                             |
|-----------------------|-----------------------------|
| 125.0 ± 1.0           |                             |
| 10                    | Length (m):                 |
| 4.5                   | Core Diameter (μm):         |
| 245.0 ± 15.0          | Coating Diameter:           |
| Optical Properties    |                             |
| 0.12                  | Numerical Aperture NA:      |
| ≤ 4.0 dB/km @ 850 nm  | Attenuation (dB/km):        |
| 770 - 1100            | Wavelength Range (nm):      |
| 5.3 ± 1.0 @ 850 nm    | Mode Field Diameter (nm):   |
| Regulatory Compliance |                             |
| <a href="#">View</a>  | Certificate of Conformance: |

## PRODUCT DETAILS

- Single Mode and Polarization Maintaining Options
- 5, 10, and 20m Lengths
- Transmission Options from 450nm to 1625nm

Bare Fiber Strands are cladless step index fibers with no sheath manufactured by Coherent and Corning to allow for easy integration in space constrained systems. These fiber spools allow for direct access to the core, facilitating precise measurements and connections as well as allowing for modification to the lengths as needed. Featuring various wavelength ranges spanning the VIS and IR spectra, these fiber spools cover a wide range of applications that require specific wavelengths and provide tight cutoff tolerances. Bare Fiber Strands are designed with core diameters of 3.0μm up to 8.2μm and numerical apertures ranging from 0.12 to 0.14.