

[See all 43 Products in Family](#)

Power Supply for 10mW HeNe Laser, 12 VDC, Bare Wire Leads



DC with Bare Leads HeNe Laser Power Supply

Stock **#18-967** **2 In Stock**

-

1

+

S\$576⁰⁰

ADD TO CART

Volume Pricing	
Qty 1+	S\$576.80 each
Need More?	Request Quote

Product Downloads



General

OEM

Type:

[1135](#), [1135P](#)

Compatible Laser Models:

L23 Series

Model Number:

[#62-726](#), [#62-727](#)

Compatible Laser Stock Number:

Physical & Mechanical Properties

4.25 x 3.30 x 1.20	Dimensions (inches):
Electrical	
2.5-25	Output Power (W):
7.5 (Max. Current Draw)	Input Current (A):
Hardware & Interface Connectivity	
3100	Output Voltage (V):
6.5	Output Current (mA):
High Voltage Alden Connector	Connector:
10-14 DC	Input Voltage (V):
Regulatory Compliance	
View	Certificate of Conformance:

Product Details

- Power Options from 0.5 - 22.5mW
- Improved Stability
- Ideal for Interferometry and Metrology Applications
- Random or Linear Polarization Options

Lumentum High Performance Helium-Neon Lasers feature a patented close-cathode design that provides improved thermal and power stability. They also utilize a patented field concentrator design that enables fast turn-on. These Lumentum HeNe lasers also feature precisely aligned cylindrical housings, with cylindrical laser heads and electrical interconnect systems used to simplify system integration. Lumentum High Performance Helium-Neon Lasers' rugged design is ideal for even the most demanding applications. They are exemplary for use within interferometry and metrology applications.

Note: Please exercise caution when using a user-provided power supply to not exceed the electrical specifications of the laser as this may cause damage and void the warranty. These HeNe lasers comply with 21CFR1040 and IEC 825-1:1993. Lumentum was previously known as JDSU.

Technical Information

Beam Expander Mounting Configurations

Click on an item below to be brought to that item's product page.

