

[See all 78 Products in Family](#)

# Preloaded Norland Optical Adhesive NOA 1622H Dispensing Barrel (10cc)

See More by [Norland](#)



10cc Dispensing Barrel for NOA (NOA60 shown as an example)

Stock **#17-381** [CONTACT US](#)

-

1

+

S\$80<sup>.50</sup>

ADD TO CART

| Volume Pricing |                               |
|----------------|-------------------------------|
| Qty 1-4        | S\$80.50 each                 |
| Qty 5-11       | S\$72.52 each                 |
| Need More?     | <a href="#">Request Quote</a> |

Product Downloads

| General  |                 |
|----------|-----------------|
| 0.34     | Size (oz):      |
| 1622H    | Norland Number: |
| 4 months | Shelf Life:     |
| Barrel   | Type:           |

|                        |                                                                                                                                 |
|------------------------|---------------------------------------------------------------------------------------------------------------------------------|
| Bonding glass to glass | Typical Applications:                                                                                                           |
|                        |                                                                                                                                 |
|                        | Note:                                                                                                                           |
|                        | Contains 10g of adhesive. This adhesive should be refrigerated between 5 - 10°C when stored to maintain its optical properties. |

| Optical Properties |                                        |
|--------------------|----------------------------------------|
| 1.622              | Index of Refraction (n <sub>d</sub> ): |
|                    |                                        |
| 315 - 395          | Absorption Range (nm):                 |
|                    |                                        |

| Material Properties |                               |
|---------------------|-------------------------------|
| Excellent           | Glass Bonding:                |
|                     |                               |
| Excellent           | Metal Bonding:                |
|                     |                               |
| Excellent           | Plastic Bonding:              |
|                     |                               |
| 220                 | Viscosity (cps):              |
|                     |                               |
| Glass to Glass      | Bonding Type:                 |
|                     |                               |
| 6                   | Energy for Full Cure (J/cm²): |
|                     |                               |

| Environmental & Durability Factors |             |
|------------------------------------|-------------|
| Soft & Flexible                    | Durability: |
|                                    |             |

| Regulatory Compliance     |                             |
|---------------------------|-----------------------------|
| <a href="#">Compliant</a> | RoHS 2015:                  |
|                           |                             |
| <a href="#">View</a>      | Certificate of Conformance: |
|                           |                             |
| <a href="#">Compliant</a> | Reach 251:                  |
|                           |                             |

## Product Details

- Dispensing Syringes Preloaded with 2 or 10g of Adhesive
  - Adhesives for Glass, Metal, and Plastic Bonding
  - Require a Dispensing Unit & Dispenser Tips for Use
  - [Applicator and Bulk Bottles](#) of Norland Adhesive Also Available
- Preloaded Norland Optical Adhesive Syringes are pneumatic dispensing syringes preloaded with either 2g or 10g of Norland Optical Adhesive. Norland Optical Adhesives are one-part, UV curing adhesives that are used for glass, metal, and plastic bonding. A range of adhesives are available to meet specific application requirements such as MIL-A-3920 for defense applications, low outgassing for aerospace applications, or UV transmission for UV optical applications. Preloaded Norland Optical Adhesive Syringes require a [dispensing unit](#) and [dispensing tips](#) for use and are ideal for applications requiring precise control of the amount of applied adhesive. Applicators and Bulk Bottles of Norland Adhesive are also available.

## Technical Information

| NORLAND OPTICAL ADHESIVES (NOA) APPLICATION NOTES    |                                                                                                                                   |
|------------------------------------------------------|-----------------------------------------------------------------------------------------------------------------------------------|
| Title                                                | Description                                                                                                                       |
| <a href="#">Applying Adhesive</a>                    | Covers best practices to use when applying Norland Optical Adhesives to ensure an even adhesive layer while avoiding air bubbles. |
| <a href="#">Chemical Resistance of NOA</a>           | Covers the effects of various chemicals on Norland Optical Adhesives including acids, bases, and solvents.                        |
| <a href="#">Preventing Lens Separations with NOA</a> | Covers best practices to avoid adhesive failures when bonding optical elements.                                                   |
| <a href="#">Separating Lenses Bonded with NOA</a>    | Covers how to unbond optical elements bonded with Norland Optical Adhesives.                                                      |