

Preloaded Norland Optical Adhesive NOA 1639H Dispensing Barrel (3cc)

See More by [Norland](#)



3cc Dispensing Barrel for NOA (NOA 60 shown as an example)

Stock **#17-403** [CONTACT US](#)

-

1

+

S\$39^{.15}

ADD TO CART

Volume Pricing	
Qty 1-4	S\$39.15 each
Qty 5+	S\$37.55 each
Need More?	Request Quote

Product Downloads

SPECIFICATIONS

General

0.1	Size (oz):
1639H	Norland Number:

4 months	Shelf Life:
Barrel	Type:
Typical Applications:	
Bonding glass to glass	
Note:	
Contains 2g of adhesive. This adhesive should be refrigerated between 5 - 10°C when stored to maintain its optical properties.	

Optical Properties

1.639	Index of Refraction (n _d):
315 - 395	Absorption Range (nm):

Material Properties

Excellent	Glass Bonding:
Excellent	Metal Bonding:
Excellent	Plastic Bonding:
240	Viscosity (cps):
Glass to Glass	Bonding Type:
6	Energy for Full Cure (J/cm²):

Environmental & Durability Factors

Soft & Flexible	Durability:
-----------------	-------------

Regulatory Compliance

Compliant	RoHS 2015:
View	Certificate of Conformance:
Compliant	Reach 247:

PRODUCT DETAILS

- Dispensing Syringes Preloaded with 2 or 10g of Adhesive
 - Adhesives for Glass, Metal, and Plastic Bonding
 - Require a Dispensing Unit & Dispenser Tips for Use
 - Applicator and Bulk Bottles of Norland Adhesive Also Available
- Preloaded Norland Optical Adhesive Syringes are pneumatic dispensing syringes preloaded with either 2g or 10g of Norland Optical Adhesive. Norland Optical Adhesives are one-part, UV curing adhesives that are used for glass, metal, and plastic bonding. A range of adhesives are available to meet specific application requirements such as ML-A-3920 for defense applications, low outgassing for aerospace applications, or UV transmission for UV optical applications. Preloaded Norland Optical Adhesive Syringes require a dispensing unit and dispensing tips for use and are ideal for applications requiring precise control of the amount of applied adhesive. Applicators and Bulk Bottles of Norland Adhesive are also available.

TECHNICAL INFORMATION

NORLAND OPTICAL ADHESIVES (NOA) APPLICATION NOTES	
Title	Description
Applying Adhesive	Covers best practices to use when applying Norland Optical Adhesives to ensure an even adhesive layer while avoiding air bubbles.
Chemical Resistance of NOA	Covers the effects of various chemicals on Norland Optical Adhesives including acids, bases, and solvents.
Preventing Lens Separations with NOA	Covers best practices to avoid adhesive failures when bonding optical elements.
Separating Lenses Bonded with NOA	Covers how to unbond optical elements bonded with Norland Optical Adhesives.

