

Power Supply for 0.5-0.8mW HeNe Laser, AC, Bare Wire Leads



AC with Bare Leads HeNe Power Supply (#11-379, #11-380)

Stock **#11-379** [CONTACT US](#)

-

1

+

S\$667⁰⁰

ADD TO CART

Volume Pricing	
Qty 1+	S\$667.00 each
Need More?	Request Quote

Product Downloads



SPECIFICATIONS

General

Type:

OEM

Compatible Laser Models:

[1108](#), [1108P](#), [1107](#), [1107P](#)

Model Number:

L92 Series

Compatible Laser Stock Number: #62-714, #62-715, #62-716, #62-717	
Features: CDRH Delay (3-5 seconds)	
Physical & Mechanical Properties	
Dimensions (inches): 4.25 x 3.30 x 1.20	
Electrical	
Output Power (W): 5	
Input Current (A): 0.55/0.32	
Hardware & Interface Connectivity	
Output Voltage (V): 1250	
Output Current (mA): 4	
Connector: High Voltage Alden Connector	
Input Voltage (V): 100/110/220 (AC)	
Regulatory Compliance	
Certificate of Conformance: View	

PRODUCT DETAILS

- Power Options from 0.5 - 22.5mW
- Improved Stability
- Ideal for Interferometry and Metrology Applications
- Random or Linear Polarization Options

Lumentum High Performance Helium-Neon Lasers feature a patented close-cathode design that provides improved thermal and power stability. They also utilize a patented field concentrator design that enables fast turn-on. These Lumentum HeNe lasers also feature precisely aligned cylindrical housings, with cylindrical laser heads and electrical interconnect systems used to simplify system integration. Lumentum High Performance Helium-Neon Lasers' rugged design is ideal for even the most demanding applications. They are exemplary for use within interferometry and metrology applications.

Note: Please exercise caution when using a user-provided power supply to not exceed the electrical specifications of the laser as this may cause damage and void the warranty. These HeNe lasers comply with 21CFR1040 and IEC 825-1:1993. Lumentum was previously known as JDSU.

TECHNICAL INFORMATION

Beam Expander Mounting Configurations

Click on an item below to be brought to that item's product page.

