

[See all 43 Products in Family](#)

Power Supply for 1.5-2.0mW HeNe Laser, AC, Bare Wire Leads



AC with Bare Leads HeNe Power Supply (#11-379, #11-380)

Stock **#11-380** **11 In Stock**

⊖ 1 ⊕ **\$663⁰⁰**

ADD TO CART

Volume Pricing	
Qty 1+	\$663.60 each
Need More?	Request Quote

Product Downloads



General

OEM **Type:**

Compatible Laser Models:
[1101](#), [1101P](#), [1103](#), [1103P](#)

L92 Series **Model Number:**

Compatible Laser Stock Number:
[#62-718](#), [#62-719](#), [#64-103](#), [#64-104](#)

CDRH Delay (3-5 seconds) **Features:**

Physical & Mechanical Properties

4.25 x 3.30 x 1.20
Dimensions (inches):

Electrical

8.33
Output Power (W):

0.55/0.32
Input Current (A):

Hardware & Interface Connectivity

1700
Output Voltage (V):

4.9
Output Current (mA):

High Voltage Alden Connector
Connector:

100/110/220 (AC)
Input Voltage (V):

Regulatory Compliance

[View](#)
Certificate of Conformance:

Product Details

- Power Options from 0.5 - 22.5mW
- Improved Stability
- Ideal for Interferometry and Metrology Applications
- Random or Linear Polarization Options

Lumentum High Performance Helium-Neon Lasers feature a patented close-cathode design that provides improved thermal and power stability. They also utilize a patented field concentrator design that enables fast turn-on. These Lumentum HeNe lasers also feature precisely aligned cylindrical housings, with cylindrical laser heads and electrical interconnect systems used to simplify system integration. Lumentum High Performance Helium-Neon Lasers' rugged design is ideal for even the most demanding applications. They are exemplary for use within interferometry and metrology applications.

Note: Please exercise caution when using a user-provided power supply to not exceed the electrical specifications of the laser as this may cause damage and void the warranty. These HeNe lasers comply with 21CFR1040 and IEC 825-1:1993. Lumentum was previously known as JDSU.

Technical Information

Beam Expander Mounting Configurations

Click on an item below to be brought to that item's product page.

