

[See all 78 Products in Family](#)

Preloaded Norland Optical Adhesive NOA 1622H Dispensing Barrel (3cc)

See More by [Norland](#)



3cc Dispensing Barrel for NOA (NOA 60 shown as an example)

Stock #17-402 [CONTACT US](#)

- 1 + **\$38^{.50}**

ADD TO CART

| Volume Pricing | |
|----------------|-------------------------------|
| Qty 1-4 | \$38.50 each |
| Qty 5-11 | \$34.72 each |
| Need More? | Request Quote |

Product Downloads

General

| | |
|----------|------------------------|
| 0.1 | Size (oz): |
| 1622H | Norland Number: |
| 4 months | Shelf Life: |
| Barrel | Type: |

Bonding glass to glass **Typical Applications:**

Note:
Contains 2g of adhesive. **This adhesive should be refrigerated between 5 - 10°C when stored to maintain its optical properties.**

Optical Properties

1.622 **Index of Refraction (n_d):**
315 - 395 **Absorption Range (nm):**

Material Properties

Excellent **Glass Bonding:**
Excellent **Metal Bonding:**
Excellent **Plastic Bonding:**
220 **Viscosity (cps):**
Glass to Glass **Bonding Type:**
6 **Energy for Full Cure (J/cm^2):**

Environmental & Durability Factors

Soft & Flexible **Durability:**

Regulatory Compliance

[Compliant](#) **RoHS 2015:**
[View](#) **Certificate of Conformance:**
[Compliant](#) **Reach 253:**

Product Details

- Dispensing Syringes Preloaded with 2 or 10g of Adhesive
- Adhesives for Glass, Metal, and Plastic Bonding
- Require a Dispensing Unit & Dispenser Tips for Use
- [Applicator and Bulk Bottles](#) of Norland Adhesive Also Available

Preloaded Norland Optical Adhesive Syringes are pneumatic dispensing syringes preloaded with either 2g or 10g of Norland Optical Adhesive. Norland Optical Adhesives are one-part, UV curing adhesives that are used for glass, metal, and plastic bonding. A range of adhesives are available to meet specific application requirements such as MIL-A-3920 for defense applications, low outgassing for aerospace applications, or UV transmission for UV optical applications. Preloaded Norland Optical Adhesive Syringes require a [dispensing unit](#) and [dispensing tips](#) for use and are ideal for applications requiring precise control of the amount of applied adhesive. Applicators and Bulk Bottles of Norland Adhesive are also available.

Technical Information

| NORLAND OPTICAL ADHESIVES (NOA) APPLICATION NOTES | |
|--|---|
| Title | Description |
| Applying Adhesive | Covers best practices to use when applying Norland Optical Adhesives to ensure an even adhesive layer while avoiding air bubbles. |
| Chemical Resistance of NOA | Covers the effects of various chemicals on Norland Optical Adhesives including acids, bases, and solvents. |
| Preventing Lens Separations with NOA | Covers best practices to avoid adhesive failures when bonding optical elements. |
| Separating Lenses Bonded with NOA | Covers how to unbond optical elements bonded with Norland Optical Adhesives. |