

Replacement Window for 1064nm foXXus Multi-Focus Objective

See More by [AdlOptica](#)



Replacement Window

Stock **#19-500** [CONTACT US](#)

⊖ 1 ⊕ **S\$142⁰⁰**

ADD TO CART

Volume Pricing	
Qty 1+	S\$142.00 each
Need More?	Request Quote

Product Downloads

General

Protective Window_D12_1064 **Model Number:**

Protective Window **Type:**

Protective window for [#19-499](#) **Note:**

Physical & Mechanical Properties

8 **Clear Aperture CA (mm):**

12.00 Diameter (mm):

Optical Properties

1064 Design Wavelength DWL (nm):

25 mJ @ 5ns Damage Threshold, By Design:

25 mJ @ 5ns Damage Threshold, Pulsed:

Regulatory Compliance

Compliant RoHS 2015:

View Certificate of Conformance:

Compliant Reach 250:

Product Details

- Focus Laser Light to 1, 2, or 4 Focal Points Along the Optical Axis
- Available with 0.38 or 0.80 Numerical Apertures
- Aplanatic Designs for 515/1030nm and 1064nm Lasers
- [AdlOptica aplanoXX Aplanatic Objectives](#) Also Available

AdlOptica foXXus Multi-Focus Objectives focus laser light to multiple foci along the optical axis, increasing the effective depth of focus and enabling high speed multilayer cutting of materials with excellent quality. Optimized for either 515/1030nm or 1064nm, these objectives are designed to be used with ultrafast solid-state and fiber lasers such as Yb:doped fiber and Nd:YAG. By manual rotation of the objective's collar, 1, 2, or 4 foci can be selected by the user. AdlOptica foXXus Multi-Focus Objectives are ideal for use in micromachining and materials processing applications to cut glass, sapphire, silicon carbide, or other brittle materials. A replaceable front window protects these objectives from damage during materials processing.

Technical Information

