

S Main Body, C-Mount, KC VideoMax



#86-889: S Main Body, C-Mount, KC VideoMax



Stock **#86-889** **2 In Stock**

1 **\$4,277⁰⁰**

ADD TO CART

Volume Pricing

| | |
|------------|-------------------------------|
| Qty 1+ | \$4,277.00 each |
| Need More? | Request Quote |

Product Downloads

General

Note:
0.2X - 0.5Xw/ Auxiliary Lens, Working Distance: 940
- 405 mm

Type:
Long Distance Microscope

Physical & Mechanical Properties

Weight (lbs):
0.54

Optical Properties

Horizontal Field of View, 1/2" Sensor:
 0.10X - 0.21X 64 - 30mm
 0.2X - 0.5X 32 - 12.8mm

Maximum Image Circle (mm):
 43.30

Primary Magnification PMAG:
 0.10X - 0.21X

Working Distance (mm):
 965 - 1,880

Sensor

Maximum Sensor Format:
 35mm (43.3mm Image Circle)

Threading & Mounting

Mount:
 C-Mount

Regulatory Compliance

RoHS 2015:
[Compliant](#)

Reach 224:
[Compliant](#)

Certificate of Conformance:
[View](#)

Product Details

- Telephoto, Macroscopic or Microscope Capability
- Focuses from Infinity to 63mm (with IF Objectives)
- Objectives Available to Provide Smaller FOVs and WDs

Designed to meet demanding imaging applications, the KC (with all 5 objectives) microscope lens provides primary magnification from 0.10-3.0X. Optional adapters for [Mitutoyo](#) and [Achrovid™](#) infinity-corrected objectives and RMS objectives allow the KC to be used as a conventional microscope, without the bulk of traditional microscope bodies or inconvenience of adapting conventional microscopes to video cameras.


This microscope lens was designed as a gauging lens, with both large working distance and high magnification. Suitable for both off-line quality control and on-line inspection in production, especially for measurement and flaw inspection. [LDL](#) and LFA adapters thread onto C-Mount. LFA provides coverage for large format cameras (F-Mount adapter included, 24 x 36mm max sensor). Interchangeable objectives thread onto main body.

A [fiber optic illuminator](#) and a [ring light guide](#) are also recommended when using the IF4 objective. A coaxial attachment, [#56-191](#) can be used for applications requiring coaxial illumination.

Motorized InFocus™ KC Video Lens

The motorized KC lens comes complete with encased focus DC Gear-motor with rubber o-ring belt drive and bracket, CE analog control unit, motor/controller cable, and CE universal power supply (110V and 220V operation). The control unit allows the user to vary focus as well as the speed and direction at which focusing occurs.

Technical Information



| Objective | IF1 | IF2 | IF3 | IF3.5 | IF4 |
|-------------------------------------|--------------|--------------|--------------|--------------|--------------|
| Primary Magnification | 0.36 - 0.75X | 0.51 - 0.91X | 0.80 - 1.28X | 1.80 - 2.29X | 2.29 - 2.98 |
| Field of View (1/2" Sensor / Horiz) | 18 - 8mm | 12.5 - 7mm | 8 - 5mm | 3.55 - 2.8mm | 2.8 - 2.15mm |
| Working Distance (mm) | 490 - 272 | 343 - 220 | 213 - 156 | 100 - 83 | 73 - 63 |

Note: Main body is required for these objectives.