

## Schneider 100mm F-Mount Lens, Short WD



Stock #85-189 [CONTACT US](#)

S\$3,900<sup>00</sup>

[ADD TO CART](#)

### Volume Pricing

Qty 1+	S\$3,900.00 each
Need More?	<a href="#">Request Quote</a>

### Product Downloads

### General

**Product Family:**  
Schneider Large Format F-Mount VIS-NIR Lenses

**Note:**  
Optimized Working Distance: 644 - 2046mm

**Type:**  
Fixed Focal Length Lens

### Physical & Mechanical Properties

**Iris Option:**  
Variable

**Length (mm):**

93.70

60.0 **Maximum Diameter (mm):**

60 **Outer Diameter (mm):**

463.00 **Weight (g):**

0.0 **Maximum Rear Protrusion (mm):**

## Optical Properties

216.00 **Field of View @ Min Working Distance (mm):**

20.4° **Horizontal Field of View, 35mm Sensor:**

43.30 **Maximum Image Circle (mm):**

100.00 **Focal Length FL (mm):**

421 - ∞ **Working Distance (mm):**

f/2.8 - f/22 **Aperture (f/#):**

<0.5 **Distortion (%):**

400 - 1000 BBAR **Coating:**

VIS-NIR Color Corrected **Lens Wavelength Range:**

## Sensor

35mm (43.3mm Image Circle) **Maximum Sensor Format:**

6.20 **Pixel Size (µm):**

## Threading & Mounting

M43.0 x 0.75 **Filter Thread:**

F-Mount **Mount:**

## Regulatory Compliance

[Compliant](#) **RoHS 2015:**

[View](#) **Certificate of Conformance:**

[Compliant](#) **Reach 233:**

## Product Details

- Full Frame, 35mm (Covers 46mm Image Circle), F-Mount Lens
- Color Corrected for Spectral Range of 400 – 1000nm
- 28mm to 100mm Focal Length

Ideal for surface inspection and line scan applications, Schneider Large Format F-Mount VIS-NIR Lenses offer low distortion and uniform performance across the entire focal plane. Featuring a lockable focus and iris, these lenses have been optically corrected for the 400 – 1000nm wavelength range. They can cover up to 35mm format sensors (43.3mm sensor diagonal). Schneider Large Format F-Mount VIS-NIR Lenses has been highly toleranced to eliminate tilt in the image plane, providing repeatable and accurate results.