

Schneider 60mm F-Mount Lens



Stock #34-234 **1 In Stock**

- 1 + \$3,037.⁰⁰

ADD TO CART

Volume Pricing

Qty 1+	\$3,037.00 each
Need More?	Request Quote

Product Downloads

SPECIFICATIONS

General

Series:
Schneider Large Format F-Mount VIS-NIR Lenses

Note:
Optimized Working Distance: 276mm - ∞

Type:
Fixed Focal Length Lens

Physical & Mechanical Properties

Variable	Iris Option:
32.60	Length (mm):
49.0	Maximum Diameter (mm):
59.6	Outer Diameter (mm):
280.00	Weight (g):
8.9	Maximum Rear Protrusion (mm):

Optical Properties

117 (35mm Sensor)	Field of View @ Min Working Distance (mm):
39.5°	Horizontal Field of View, 35mm Sensor:
60.00	Maximum Image Circle (mm):
60.00	Focal Length FL (mm):
200 - ∞	Working Distance (mm):
f/4.0 - 4/16	Aperture (f/#):
<0.6	Distortion (%):
400 - 1000 BBAR	Coating:
MS-NIR Color Corrected	Lens Wavelength Range:

Sensor

60mm (Image Circle)	Maximum Sensor Format:
6.20	Pixel Size (µm):

Threading & Mounting

M43.0 x 0.75	Filter Thread:
F-Mount	Mount:

Regulatory Compliance

Compliant	RoHS 2015:
View	Certificate of Conformance:
Compliant	Reach 233:

PRODUCT DETAILS

- Full Frame, 35mm (Covers 46mm Image Circle), F-Mount Lens
- Color Corrected for Spectral Range of 400 – 1000nm
- 28mm to 100mm Focal Length

Ideal for surface inspection and line scan applications, Schneider Large Format F-Mount VIS-NIR Lenses offer low distortion and uniform performance across the entire focal plane. Featuring a lockable focus and iris, these lenses have been optically corrected for the 400 – 1000nm wavelength range. They can cover up to 35mm format sensors (43.3mm sensor diagonal). Schneider Large Format F-Mount VIS-NIR Lenses has been highly toleranced to eliminate tilt in the image plane, providing repeatable and accurate results.