

SCHOTT BG66, 100 x 80mm, 4.5mm Thick, Matte Plate Bandpass Filter

See More by [SCHOTT Optical Components](#)



Stock #26-911 **4 In Stock**

- 1 + \$547⁰⁰

ADD TO CART

Volume Pricing

Qty 1-10	\$547.40 each
Qty 11+	\$483.00 each
Need More?	Request Quote

Product Downloads

General

Bandpass Filter **Type:**

Physical & Mechanical Properties

100.0 x 80.0 **Dimensions (mm):**

100.00 **Length (mm):**

Thickness (mm):

4.50 ±0.5

Width (mm):

80.00

Edges:

Break Edges

Optical Properties

Center Wavelength CWL (nm):

514.00

Glass/Filter Number:

[SCHOTT BG66](#)

Coating:

Uncoated

Color:

Blue-Green

Index of Refraction (n_d):

1.54

Wavelength:

NIR Cutoff

Material Properties

Density (g/cm³):

2.85

Transformation Temperature (°C):

416

Regulatory Compliance

Certificate of Conformance:

[View](#)

Product Details

- Unpolished Colored Glass Plates
- Large Raw Material Sizes up to 165 x 165mm
- Available in All [SCHOTT Colored Glass Types](#)
- [Polished SCHOTT Colored Glass Filters](#) Also Available

SCHOTT Matte Colored Glass Filter Plates are unpolished plates of colored glass that are used as raw material to manufacture [SCHOTT Colored Glass Filters](#). With large standard sizes up to 165 x 165mm, these plates can be cut, ground, and polished to meet application requirements for a wide range of filter sizes. SCHOTT Matte Colored Glass Filter Plates are available in all [SCHOTT colored glass types](#), including shortpass (heat absorbing), longpass, bandpass, and neutral density. To learn more about how our custom optical colored glass filter capabilities can be used for your application, see our [capabilities page](#).

Quote Your Size