

SCHOTT N-WG280, 12.5mm Dia., 1mm Thick, Colored Glass Longpass Filter

See More by [SCHOTT Optical Components](#)



Stock #16-403 3-5 DAYS



1



S\$46.40

ADD TO CART

Qty 1-10

S\$46.40

Qty 11+

S\$40.60

Volume Pricing

[Request Quote](#)

Get Product Downloads

Diameter (mm):
12.50

Cut-On Wavelength (nm):
280.00 ±6

Density (g/cm³):

2.51
Glass/Filter Number: SCHOTT N-WG280
Coating: Uncoated
Color: Clear
Passband Limit 1 λ_{p1} (nm): 380
Index of Refraction n_d: 1.52
Spectral Transmittance t_p (%): 99
Stopband Limit λ_s(nm): 230
Surface Quality: 60-40
Transformation Temperature (°C): 558
Thickness (mm): 1.00 ±0.1
Type: Longpass Filter
Wavelength: UV
Dimensional Tolerance (mm): ±0.2
Reflection Factor P_d: 0.92
Bevel: Protective as needed

Regulatory Compliance

Certificate of Conformance: View
--