

SCHOTT N-WG320, 12.5mm Dia., 2mm Thick, Colored Glass Longpass Filter

See More by [SCHOTT Optical Components](#)



Stock #16-433 3-5 DAYS

- 1 +

S\$46.40

ADD TO CART

Qty 1-10
S\$46.40
Qty 11+
S\$40.60
Volume Pricing
Request Quote

Get Product Downloads

Diameter (mm):
12.50

Cut-On Wavelength (nm):
320.00 ±6

Density (g/cm³):

2.51
Glass/Filter Number: SCHOTT N-WG320
Coating: Uncoated
Color: Clear
Passband Limit 1 λ_{p1} (nm): 470
Index of Refraction n_d: 1.52
Spectral Transmittance t_p (%): 92
Stopband Limit λ_s(nm): 280
Surface Quality: 60-40
Transformation Temperature (°C): 563
Thickness (mm): 2.00 ±0.2
Type: Longpass Filter
Wavelength: UV
Dimensional Tolerance (mm): ±0.2
Reflection Factor P_d: 0.92
Bevel: Protective as needed

Regulatory Compliance

Certificate of Conformance: View
--