

[See all 7 Products in Family](#)

Solarization-Resistant Reflection/Backscatter Probe, Silicone-coated steel monocoil

See More by [Ocean Optics](#)



Stock #90-562 **NEW** 1 In Stock

⊖ 1 ⊕ S\$1,624⁰⁰

ADD TO CART

Volume Pricing

| | |
|------------|-------------------------------|
| Qty 1+ | S\$1,624.00 each |
| Need More? | Request Quote |

Product Downloads

General

Model Number:
QR400-7-VIS-NIR

Title:
Solarization-Resistant Reflection/Backscatter Probe,
Silicone-coated steel monocoil

Optical Properties

Wavelength Range (nm):
180 - 1100

Regulatory Compliance

[Compliant](#) **RoHS 2015:**

[View](#) **Certificate of Conformance:**

[Compliant](#) **Reach 250:**

Product Details

- Versatile Sampling for Diffuse/Specular Reflectance, Backscatter & Fluorescence
- VIS-NIR (400–2100nm) and UV-VIS (180–1100nm) Solarization-Resistant Models
- Extreme Solarization-Resistant (XSR) Probe Features Ultra-Low Loss Fiber for Harsh UV Exposure
- Connects Directly with Ocean Optics Spectrometers & Accessories

Ocean Optics Reflection/Backscatter Probes are compact, fiber-coupled sampling tools for measuring diffuse and specular reflectance, backscatter, or fluorescence in solids, solutions, or powders, and connect directly with [Ocean Optics Spectrometers and Accessories](#). They provide quantitative insights into a sample's color, appearance, and chemical composition. Choose from Visible-NIR, Solarization-Resistant, or XSR models for applications ranging from routine reflectance to demanding UV measurements. With durable jacketing, precision ferrules, and solarization-resistant fiber, the rugged design ensures reliable performance even in harsh conditions. Ocean Optics Reflection/Backscatter Probes can be optimized for UV applications, with the XSR probe featuring ultra-low loss fiber designed to withstand harsh UV exposure.