

TECHSPEC[®] Sliding 2" x 3" Base Plate



Stock #03-655 20+ In Stock

-

1

+

S\$34^{.80}

ADD TO CART

Volume Pricing	
Qty 1-9	S\$34.80 each
Qty 10+	S\$30.89 each
Need More?	Request Quote

Product Downloads

SPECIFICATIONS

General

Type:

English

Physical & Mechanical Properties

Length (mm):

76.20	
	Width (mm):
50.80	
	Thickness (mm):
9.50	
	Construction:
Black Anodized Aluminum	
	Number of Slots:
2	

Regulatory Compliance

	RoHS 2015:
Compliant	
	Certificate of Conformance:
View	

	Reach 250:
Compliant	

PRODUCT DETAILS

- Increase the Versatility of Existing Mounting Equipment
- Ideal for Direct Mounting to Standard Breadboards
- Counterbored 1/4-20 or M6 x 1.0 Holes/Slots

TECHSPEC® Slotted 2" x 3" Base Plates are versatile mounting surfaces for breadboard and optical rail applications. Three 6.4mm diameter counterbored holes, ideal for 1/4"-20 hardware, allow posts or post holders to be mounted directly and can also accommodate a variety of other optomechanical components. The plates are ideal for adding extra versatility and adjustment capability to a benchtop optical system. TECHSPEC® Slotted 2" x 3" Base Plates are available in standard sliding or side to side sliding configurations, allowing for adjustment along or perpendicular to the optical axis of the system.

TECHNICAL INFORMATION

