


**TECHSPEC® T-Mount Iris Diaphragm Mount**



T-Mount Iris Diaphragm Mount, #52-299

Stock **#52-299** **1 In Stock**

⊖ 1 ⊕ **S\$316<sup>00</sup>**

**ADD TO CART**

Volume Pricing	
Qty 1-4	<b>S\$316.40</b> each
Qty 5-9	<b>S\$279.16</b> each
Qty 10-25	<b>S\$257.60</b> each
Need More?	<a href="#">Request Quote</a>

Product Downloads

**General**

Iris Diaphragm **Function:**

**Physical & Mechanical Properties**

18.13 **Extension Length (mm):**

22.0 **Total Length (mm):**

1.2 - 30.0      Clear Aperture CA (mm):

58.0      Outer Diameter (mm):

## Threading & Mounting

T-Mount      Thread Type:

## Regulatory Compliance

Compliant      RoHS 2015:

Compliant      Reach 219:

View      Certificate of Conformance:

## Product Details

- Variable Apertures for C, S, and T-Mount Systems
- Male and Female Thread at Opposite Ends for Easy Integration
- Adjusted via Rotating Ring or Lever for Precision Control

TECHSPEC® C, S, and T-Mount Iris Diaphragm Mounts feature iris diaphragms that allow for precision control over the internal aperture within a system. Using male and female threads, these mounts can be placed anywhere within a C, S, or T-Mount system. The apertures can be adjusted via a rotating ring for the C-Mount version, with a 4mm lever for the S-Mount version and with a 5mm lever for the T-Mount version. TECHSPEC C, S, and T-Mount Iris Diaphragm Mounts add 12mm, 12mm, and 18mm to the system length, respectively. These mounts are ideal for providing control over the  $f\#$ , field stop diameter, and overall energy throughput of a C, S, or T-Mount system.

**NOTE:** The iris planes sit approximately 15mm, 8mm, and 12mm from the female ends of the TECHSPEC C, S, and T-Mount Iris Diaphragm Mounts, respectively.

## Technical Information

