

SWIR Inline Tube Lens



SWIR Inline Tube Lens

Stock **#26-223** **1 In Stock**

⊖ 1 ⊕ **\$8,694⁰⁰**

ADD TO CART

Volume Pricing	
Qty 1+	\$8,694.00 each
Need More?	Request Quote

Product Downloads

Optical Properties

Magnification:
1X

Wavelength Range (nm):
900 - 1700

Sensor

Maximum Sensor Format:
1.1"

Threading & Mounting

C-Mount

Mount:

M26

Mounting Threads:

Regulatory Compliance

[View](#)

Certificate of Conformance:

Product Details

- High-Resolution for Short Wave Infrared (SWIR) Wavelengths up to 1600nm
- Available in Magnifications of 1x to 50X
- Ideal for Photo Emission Detection, Laser Marking, and Laser Cutting

SWIR Plan APO Infinity Corrected Objectives are high resolution objective lenses with long working distances that are color corrected between 800 – 1600nm. Available in magnifications of 1X to 50X, these objectives feature high numerical apertures for high resolution imaging at SWIR wavelengths. With a common 95mm parfocal length, these objectives can be combined with a 200mm focal length tube lens and a compatible [C-mount camera](#) for easy system integration. SWIR Plan APO Infinity Corrected Objectives are ideal for Photo Emission Detection, Wafer Backside Inspection, Laser Glass Cutting, and Laser Scan Microscopy applications.
