

[See all 10 Products in Family](#)

# UV-VIS-NIR Nd:YAG Laser Line Vertical Mitutoyo Video Microscope Unit

See More by [Mitutoyo](#)



Stock #71-017 [CONTACT US](#)

⊖ 1 ⊕ **SS\$17,500<sup>00</sup>**

**ADD TO CART**

#### Volume Pricing

Qty 1+	<b>SS\$17,500.00</b> each
Need More?	<a href="#">Request Quote</a>

**Note:** This item requires accessories for use | [Learn More](#)

#### Product Downloads

#### General

378-508 **Model Number:**

UV-VIS-NIR **Range:**

Vertical Mount, Brightfield, Erect Image **Type:**

Mitutoyo **Manufacturer:**

**Compatible Objectives:**  
MPlan Apo/HR/SL, MPlan NIR/NUV, and MPlan UV

**Note:**  
Note: Magnification: 1X Tube Lens Optional C-Mount adapter #37-044 available for dual-camera system

## Physical & Mechanical Properties

**Weight (g):**  
1300

## Optical Properties

**Design Wavelength DWL (nm):**  
266, 355, 523, 1064nm

**Magnification:**  
1X

## Sensor

**Maximum Sensor Format:**  
2/3"

## Threading & Mounting

**Mount:**  
C-Mount

**Mounting Threads:**  
Objective Mounts: M26 x 36 TPI

## Regulatory Compliance

**RoHS 2015:**  
[Exempt](#)

**Certificate of Conformance:**  
[View](#)

**REACH 241:**  
[Contains SVHC\(s\)](#)

## Product Details

- Designed for use with [Mitutoyo NIR, NUV, and UV Infinity Corrected Objectives](#)
- Maximum Sensor Size up to 2/3"
- Ideal for Laser Processing and Machining applications

Mitutoyo Nd:YAG Laser Line Video Microscope Units (VMU) allow for quick and easy setup of laser processing systems by connecting an infinity corrected objective to a c-mount camera. Optimized for Nd:YAG laser lines of 266, 355, 532, and 1064nm, these VMUs are designed for use with [Mitutoyo UV, NUV, and NIR infinity corrected objectives](#). These VMUs can also be used as infrared inspection systems when using an infrared light source and an infrared camera. Mitutoyo Nd:YAG Laser Line Video Microscope Units (VMU) are ideal for laser processing and imaging applications such as cutting, trimming, and repair of IC wiring, thin-film processing, and infrared spectral characteristic analysis. A dual-camera laser line VMU option is also available for high and low magnification observation.