

White LED Ring Light



Stock **#63-306** CLEARANCE **2 In Stock**

-

1

+

S\$882^{.00}

ADD TO CART

Volume Pricing	
Qty 1+	S\$882.00 each
Need More?	Request Quote

Product Downloads

SPECIFICATIONS

General	
100,000	LED Lifetime (hours):
N/A	Irradiance at 40mm (W/m²):
LED Illuminator	Type of Illumination:
Ring Light	Geometry:

Illumination Mode:	
Strobed or Constant	
Physical & Mechanical Properties	
Diameter (mm):	
74.20	
Height (mm):	
17.00	
Optical Properties	
Color:	
White	
Spot Size at 40mm Working Distance (mm):	
65.00	
Hardware & Interface Connectivity	
Power Supply:	
Power Supply Required and Sold Separately:	
USA: #59-433	
Europe: Not Available	
Japan: #59-433	
Korea: Not Available	
China: #59-433	
Threading & Mounting	
Mounting Threads:	
(4) M3	
Regulatory Compliance	
RoHS 2015:	
Compliant	
Reach 209:	
Compliant	
Certificate of Conformance:	
View	

PRODUCT DETAILS

[#59-433](#) Universal Power Supply is required for operation. [#63-343](#) Ring Light Heat Sink is recommended to maintain performance and optimize product lifetime.

- Variable Intensity with DC Current Controller
- Excellent Uniformity
- 100,000 Hour Product Lifetime
- [Heat Sinks and Power Supplies](#) Sold Separately

Compact LED Ring Lights provide the high-power illumination required in machine vision, biomedical, fluorescence, and strobing applications. Each LED module contains four M3 mounting holes on a 29mm diameter circle. The universal power supply, which accepts a 90 - 245VAC input, ships with clip-on adapters for the US, Europe, and UK. Through the DIN rail mountable DC current controller, LED intensity can be adjusted manually via a potentiometer or by supplying a 0 - 5V analog control input. The DC current controller is designed to deliver up to 400mA at 24V.

Note: [#59-433](#) Universal Power Supply is required for operation. [#63-343](#) Ring Light Heat Sink is recommended to maintain performance and optimize product lifetime.